


FEATURES

- **Annealed Copper Conductor:** Offers superior conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Provides excellent insulation and protection against environmental factors
- **Plain Conductor Type:** Ensures consistent performance and ease of installation
- **32/0.2 Core Strands:** Enhances flexibility and durability
- **3 Cores:** Suitable for a variety of electrical applications
- **Operating Temperature Range -15 °C to 90 °C:** Suitable for diverse environments
- **Voltage Rating of 500 V:** Ideal for medium voltage applications
- **8 mm Outside Diameter:** Compact design for easy routing and installation

RS PRO 1 mm² Flexible Cable, 50 m Length

RS Stock No: 606-112



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable's PVC jacket provides robust protection, making it suitable for environments with varying temperatures.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1 mm ²
Cable Length	50 m
Core Strands	32/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	8 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------