





Page 1 of 14 Pages

No.: RZUN2023-2404

# 检测报告 TEST REPORT

**UN38.3** 

NAME OF SAMPLE:	Li-Polymer Rechargeable Battery				
产品名称:	聚合物锂离子电池				
CLIENT: 委托单位:	Teledyne FLIR Commercial Systems, Inc. Taiwan Branch 美商特勵達菲力爾股份有限公司台灣分公司				
CLASSIFICATION OF TEST: 检测类别:	Commission Test 委托测试				

威凯检测技术有限公司 CVC Testing Technology Co., Ltd.

## 检测报告

### **TEST REPORT**

No.:RZUN2023-2404 Page 2 of 14 Pages

Name of samples: Li-Polymer Rechargeable Battery	Type/Model: 型号规格: IP604480P-2P
样品名称:聚合物锂离子电池 Color: Blue	3,7V 5400mAh 20,0Wh Physical shape:Prismatic
样品颜色:蓝色	样品形状:棱柱形
Commissioned by: Teledyne FLIR Commercial Systems, Inc. Taiwan Branch 委托单位: 美商特勵達菲力爾股份有限公司台灣分公司	Commissioner address:10F, No. 57, Zhouzi Street, NeiHu District, Taipei city , Taiwan 委托单位地址:台灣省台北市内湖區洲子街 57 號 10 樓
Manufacturer: RPC Corporation 制造商: 聚力電子股份有限公司	Manufacturer address:17F-5, No. 716, Zhongzheng Rd., Zhonghe District, New Taipei City, Taiwan 制造商地址: 台灣新北市中和區中正路 716 號 17 樓之 5
Factory: Intellect Pioneering Battery Technology Co.,Ltd. 生产厂: 佛山市顺德区精锐电池科技有限公司	Factory address: No.30 Xinghua Road East, Xinghua Industrial Park, Ronggui Street, Shunde District, Foshan, Guangdong, China 生产厂地址: 中国广东省佛山市顺德区容桂街道兴华工业区兴华东路 30 号
Classification of test: Commission Test 检测类别: 委托测试	Quantity of sample: 8 battery packs, 30 cells 样品数量: 8 个电池组, 30 个电芯
Tested according to: 测试标准: ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3	Sample identification: 样品标识序号:b1#~b8#, c1#~c30#
Receiving date: 接样日期: 2023-05-12	Means of receiving: Submitted by commissioner 接样方式: 委托单位送样
Completing date: 完成日期: 2023-06-01	Test item: 8 items 测试项目: 8 项

### Test conclusion:

检测结论:

The Li-Polymer Rechargeable Batteries submitted by Teledyne FLIR Commercial Systems, Inc. Taiwan Branch are tested according to Section 38.3 of the Seventh revised edition Amendment 1 of the Manual of Tests and Criteria (ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3). The test items are full items. The test results comply with the relevant requirements of the standard.

由美商特勵達菲力爾股份有限公司台灣分公司送检的聚合物锂离子电池,依据联合国《试验和标准手册》 第七修订版修正 1 第 38.3 节进行检测,试验为全项目,试验结果符合标准相关要求。

> Seal of CVC CVC 盖章 Date of issue:2023-06-30 签发日期:

Title:Manager批准人职务:经理

Approved by: Huang Kun Reviewed by: Zhang Siyao Tested by: Zheng Feida

批准: Huengen 审核: Zhang siyon 检验: XhangFesh

Description and illustration of the sample:

样品说明及描述:

The sample's status is good

样品状况良好。

The battery (IP604480P-2P) is composed of cells (IP604480), and the connection mode is: 2P1S 电池组(IP604480P-2P)由电芯(IP604480)组成,连接方式为: 2P1S

Cell Dimensions/电芯尺寸: 6mm\*44mm\*80mm

Watt-hour rating of each battery/ 单个电池组的瓦时率: 20,0Wh

Test item	Sample No.	State	Remark
试验项目	样品编号	状态	备注
	b1#~b4#	at first cycle, in fully charged states 第一个交替充电放电周期完全充电状态	-
T.1~T.5	b5#~b8#	after 25 cycles ending in fully charged states 第 25 个交替充电放电周期完全充电状态	-
To	c1#~c5#	at first cycle at 50% of the design rated capacity 第一个交替充电放电周期充电到设计额定容量的 50%	
T.6	c6#~c10#	after 25 cycles ending at 50% of the design rated capacity 第 25 个交替充电放电周期充电到设计额 定容量的 50%	-
	b1#~b4#	at first cycle, in fully charged states 第一个交替充电放电周期完全充电状态	using undamaged samples previously
T.7	b5#~b8#	after 25 cycles ending in fully charged states 第 25 个交替充电放电周期完全充电状态	used in tests T.1 to T.5 使用试验 T.1 至 T.5 未 损坏的样品
	c11#~c20#	at first cycle, in fully discharged states 第一个交替充电放电周期完全放电状态	-
T.8	c21#~c30#	after 25 cycles ending in fully discharged states 第 25 个交替充电放电周期完全放电状态	-

The test objects of T.1~T.5 and T.7 are battery packs, and the sample numbers are b1#~b8# T.1~T.5、T.7 的测试对象为电池组,样品编号为 b1#~b8#。

The test objects of T.6 and T.8 are component cells, and the sample numbers are c1#~c30# T.6、T.8 的测试对象为组成电芯,样品编号为 c1#~c30#。

D	escription	of the	sampling	procedure:

取样程序的说明:

/

Description of the deviation from the standard, if any:

试验结果不符合标准项的说明:

/

#### Remarks:


备注:


Throughout this report a comma is used as the decimal separator.


本报告中以逗号代替小数点。

### Photos of Samples and Labels/样品照片及标识

Battery/电池 (IP604480P-2P 3,7V 5400mAh 20,0Wh)









### Photos of Samples and Labels/样品照片及标识

Component Cell/内部电芯(IP604480 3,7V 2700mAh 9,99Wh )







ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3							
Clause 章节	Requirements 标准要求	Result 测试结果	Verdict 判定				
38.3.4	Procedure/试验步骤	•	_				
	Test T.1: Altitude simulation/试验 T.1: 高度模拟	Į.					
	Test cells and batteries shall be stored at a pressusix hours at ambient temperature (20±5℃)/ 将电压力为不大于 11,6kpa 的环境中贮存不少于 6 个小	芯和电池在温度为 20±5℃,大气					
38.3.4.1	Requirement/标准要求: 1 Cells and batteries Mass loss limit: ≤0,1% /样品质量损失≤0,1% 2 Open circuit voltage not less than 90%, The	The samples b1#~b8# : No leakage, no venting, no	P				
	requirement relating to voltage is not applicable to test cells and batteries at full discharged states. 样品试验后开路电压应不低于试验前开路电压的	disassembly, no rupture and no fire/编号为 b1#~b8#的样品: 无漏液、无排气、无解体、无破裂以及无着火现象					
	90%,此要求不适用于完全放完电的电池和电芯。 3 No leakage, no venting, no disassembly, no rupture and no fire 样品(电池)应无漏液、无排气、无解体、无破裂以及无着火现象的发生						
	Test T.2: Thermal test/试验 T.2: 温度试验						
	Test cells and batteries are to be stored for/电池存储条件如下:						
	1 For small cells and batteries: one temperature cycle: 72±2°C(6h) —-40±2°C(6h)						
	/对于小型电芯和电池: 一次温度循环为 <b>72±2℃(6h)</b> —- <b>40±2℃(6h)</b>						
	For large cells and batteries: one temperature cyc	cle: 72±2°C(12h) —-40±2°C(12h)					
	/对于大型电芯和电池: 一次温度循环为 <b>72±2℃(12h)</b> —- <b>40±2℃(12h)</b>						
	2 The maximum time interval between test temperature extremes is 30 minutes/温度转换最大间隔时间为 30min						
	3 This procedure is to be repeated 10 times/重复 10 次循环						
38.3.4.2	4 after which all test cells and batteries are to be stored for 24 hours at ambient temperature (20±5℃)/循环结束后,电池在 20±5℃的条件下 搁置 24 小时						
	Requirements/标准要求						
	1 Cells and batteries Mass loss limit: ≤0,1% /样 品质量损失≤0,1%	The samples b1#~b8# :					
	2 Open circuit voltage not less than 90%, The requirement relating to voltage is not applicable to test cells and batteries at full discharged states. 样品试验后开路电压应不低于试验前开路电压的90%,此要求不适用于完全放完电的电池和电芯。3 No leakage, no venting, no disassembly, no	No leakage, no venting, no disassembly, no rupture and no fire/编号为 b1#~b8#的样品: 无漏液、无排气、无解体、无破裂以及无着火现象 The data is shown in Table 1./					
	rupture and no fire 样品(电池)应无漏液、无排气、无解体、无破 裂以及无着火现象的发生	数据见表 1					

ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3									
Clause	e Requirements Result								
章节	标准要求	测试结果	判定						
Clause 章节	Requirements 标准要求  Test T.3: Vibration/试验 T.3: 振动  1 Cells and batteries are firmly secured to the platt 芯和电池牢固地安装在振动台(的台面)上 2 The vibration: a sinusoidal waveform with a loga 200Hz and back to 7Hz traversed in 15 minutesy 至 200Hz,然后在减少回到 7Hz 为一个循环,一定送。 3 For cells and small batteries: from 7 Hz a peak a until 18Hz is reached. The amplitude is then matexcursion) and the frequency increased until a p (approximately 50Hz). A peak acceleration of 8 frequency is increased to 200Hz. / 对于电芯和小型值加速度保持不变,直到达到 18Hz。然后将振幅设并且频率增加直到出现 8gn 的峰值加速度(大约 50度,直到频率增加到 200Hz。  For large batteries: from 7Hz a peak acceleration or reached. The amplitude is then maintained at 0,8the frequency increased until a peak acceleration of 2gn is then maincreased to 200Hz. / 对于大型电池:从 7Hz 开变,直到达到 18Hz。然后将振幅保持在 0,8mm(到出现 2gn 的峰值加速度(大约 25Hz)。然后保护加到 200Hz。 4 This cycle repeated 12 times for a total of 3 h perpendicular mounting position of the cell. One obe perpendicular to the terminal face. /以振动的性,对每个电芯从三个互相垂直的方向上循环 12 分时。 Requirements/标准要求 1 Cells and batteries Mass loss limit: ≤0,1% /样品质量损失≤0,1% 2 Open circuit voltage not less than 90%, The	Result 测试结果  form of the vibration machine /电 rithmic sweep between 7Hz and 振动以正弦波形式,以 7Hz 增加 介循环持续 15 分钟的对数前移传 acceleration of 1gn is maintained intained at 0,8mm (1,6mm total beak acceleration of 8gn occurs gn is then maintained until the 早电池:从 7Hz 开始,以 1gn 的峰民并在 0,8mm(总偏移 1,6mm)的Hz)。然后保持 8gn 的峰值加速 of 1gn is maintained until 18Hz is mm (1,6mm total excursion) and on of 2gn occurs (approximately intained until the frequency is 始,以 1gn 的峰值加速度保持不总偏移 1,6mm)并且频率增加直持 2gn 的峰值加速度,直到频率增加,以 1gn 的峰值加速度, 1gn 的域的, 1gn 的, 1gn 的	Verdict 判定						
	样品(电池)应无漏液、无排气、无解体、无破 裂以及无着火现象的发生								

ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3								
Clause	Requirements Result							
章节	标准要求	测试结果	判定					
Clause 章节		Result 测试结果  sting machine/以稳固的托架固 of peak acceleration of 150 gn ay be subjected to a half-sine on of 11 milliseconds. / 对每个续6毫秒,大型电芯须经受最估。 ck of peak acceleration of 150 lller) and pulse duration of 6 half-sine of peak acceleration maller) and pulse duration of $150  \mathrm{mass}$ 中的较小值)的半正经受最大加速度 $150  \mathrm{mass}$ 中的较小值)的半正经受最大加速度 $150  \mathrm{mass}$ 中的较小值)的半正经受最大加速度 $150  \mathrm{mass}$ 中的较小值)的半正是不可以表现的证据, $150  \mathrm{mass}$ 中的较小值)的半正是不可以可以可以可以可以可以可以可以可以可以可以可以可以可以可以可以可以可以可以	Verdict 判定					

	ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3						
Clause 章节	Requirements 标准要求	Result 测试结果	Verdict 判定				
	Test T.5: External Short Circuit/试验 T.5 外部短路	}					
38.3.4.5	1The cell or battery to be tested shall be heated for a period of time necessary to reach a homogeneous stabilized temperature 57±4℃/加热电芯或电池样品直到温度稳定在 57±4℃  2 The cell or battery shall be subjected to a short circuit condition with a total external resistance of less than 0,1 ohm at 57±4℃, This short circuit condition is continued for at least one hour after the cell or battery external case temperature has returned to 57±4℃, or in the case of the large batteries, has decreased by half of the maximum temperature increase observed during the test and remains below that value. /将样品正负极用小于 0,1Ω 的总电阻回路进行短路,样品的外表温度恢复到 57±4℃之后保持短路状态 1 小时以上;对于大电池,电池温度降低至最高温升值的一半时实验结束。  3 The cell or battery must be observed for a further six hours for the test to be						
	concluded, /对电芯或电池必须进一步观察 6 个小时才能下结论。						
	Requirements/标准要求: During the test and within six hours after test ,the cells or batteries 在试验过程中以及之后 6 个小时内,电芯或电池样品  1. External temperature not exceed 170°C 外表温度不超过 170°C  2. No disassembly, no rupture and no fire. 无解体、无破裂和无着火现象发生。						

ST/SG/AC.10/11/Rev.7/Amend.1/Section 38.3						
Clause	Requirements	Result	Verdict			
章节	标准要求	测试结果	判定			
	Test T.6: Impact / Crush / 试验 T.6: 撞击/挤压		Р			
	Impact (applicable to cylindrical cells not less than 1 撞击(适用于直径不小于 18 毫米的圆柱形电池)	8mm in diameter) /				
	1 This test sample cell or component cell is to be placed on a flat smooth surface/ 将试验样品用的电芯或聚合物电芯放在一个平坦光滑的平面上 2 A 15,8 mm diameter bar is to be placed across the centre of the sample, A 9,1kg mass is to be dropped from a height of 61±2,5cm onto the sample./将一直径为 15,8mm 的不锈钢圆棒横过电池中部放置后,将一质量为 9,1kg 的物体从 61±2,5cm 的高度落向样品。 3 The test sample is to be impacted with its longitudinal axis parallel to the flat surface and perpendicular to the longitudinal axis of the 15,8 mm ± 0,1mm diameter curved surface lying across the centre of the test sample. Each sample is to be subjected to only a single impact./ 接受撞击的试样,纵轴应与平坦的表面平行并与横放在试样中心的直径 15,8±0,1 毫米弯曲表面的纵轴垂直。每一个试样只经受一次撞击。					
	Requirements/标准要求: 1 Cells external temperature not exceed 170℃.电芯或电池的最高表面温度应不超过 170℃ 2 No disassembly, no fire within six hours of this test 试验结束后 6 个小时之内,电芯和聚合物电芯应无解体和无着火现象发生	-				
38.3.4.6	Crush (applicable to prismatic, pouch, coin/button than 18mm in diameter) / 挤压(适用于棱柱形、袋装、硬币/纽扣电池和直径 1 A cell or component cell is to be crushed be crushing is to be gradual with a speed of approxim of contact. The crushing is to be continued until the is reached. / 将电池或元件电池放在两个平面之间打一个接触点上的速度大约为 1,5 厘米/秒。挤压持续过一: (a) The applied force reaches 13 kN ± 0,78 kN. / 施建设置 (b) The voltage of the cell drops by at least 100 mV, (c) The cell is deformed by 50% or more of its origing 厚度的 50%以上。 2. A prismatic or pouch cell shall be crushed by a side. A button/coin cell shall be crushed by applying For cylindrical cells, the crush force shall be longitudinal axis. /棱柱形或袋装电池应从最宽的一直平坦表面施压。圆柱形应从与纵轴垂直的方向施压。Requirements/标准要求: 1 Cells external temperature not exceed 170°C.电芯或电池的最高表面温度应不超过 170°C 2 No disassembly, no fire within six hours of this test 试验结束后 6 个小时之内,电芯和聚合物电芯应无解体和无着火现象发生	小于 18 毫米的圆柱形电池) etween two flat surfaces. The ately 1,5 cm/s at the first point first of the three options below 济压,挤压力度逐渐加大,在第进行,直到出现以下三种情况之加的力达到 13kN±0,78kN/电池的电压下降至少 100 毫伏 final thickness./电池变形达原始 pplying the force to the widest g the force on its flat surfaces. applied perpendicular to the	P			

	ST/SG/AC.10/11/Rev.7/Amend.1/S	Section 38.3				
Clause 章节	Requirements 标准要求	Result 测试结果	Verdict 判定			
38.3.4.7	Test T.7: Overcharge/试验 T.7: 过度充电  1 The charge current shall be twice the manufacturer's recommended maximum continuous charge current/以 2 倍制造厂推荐的最大持续充电电流对样品充电 2 The minimum voltage of the test shall be as follows/本试验最小电压见下文					
	a) When the manufacturer's recommended charge voltage is not more than 18V, the minimum voltage of the test shall be the lesser of two times the maximum charge voltage of the battery or 22V/ 如果厂家推荐的充电电压不超过 18V,本试验的最小充电电压应是厂家标定最大充电电压的两倍或者是 22V 之中的较小者。	The voltage of the test is				
	b) When the manufacturer's recommended charge voltage is more than 18V, the minimum voltage of the test shall be 1,2 times the maximum charge voltage/ 如果厂家推荐的充电电压超过 18V,本试验的最小充电电压应是厂家标定最大充电电压的1,2倍。	8,5V, and the current is 5,2A 试验的电压为 8,5V, 电流为 5,2A	P			
	3 Tests are to be conducted at ambient temperature 20±5°C, The duration of the test shall be 24 hours/20±5°C的环境温度下,试验持续 24 小时。					
	Requirements/标准要求: No disassembly and no fire within seven days of this test 试验样品在试验中和试验后 7 天内,应无解体和无	The samples b1#~b8#: no disassembly and no fire/ 编号为 b1#~b8#的样品:无 解体、无着火现象				
	着火现象发生。	For voltage data before test, see table 3. / 试验前电压见表 3				
	Test T.8: Forced discharge/试验 T.8: 强制放电					
	Each cell shall be forced discharged at ambient temperature by connecting it in series with a 12 V D.C. power supply at an initial current equal to the maximum discharge current specified by the manufacturer,					
	20±5℃的环境温度下,将单个电芯连接在 12V 的直流   电源提供给每个电芯初始电流为制造厂指定的最大放					
38.3.4.8	The specified discharge current is to be obtained by connecting a resistive load of the appropriate size and rating in series with the test cell. Each cell shall be forced discharged for a time interval (in hours) equal to its rated capacity divided by the initial test current (in ampere)					
	指定的放电电流通过串联在试验电芯上的合适大小和 的强制放电时间(小时)为额定容量除以初始电流(					
	Requirements/标准要求: No disassembly and no fire within seven days of this test	The samples c11#~c30#: no disassembly and no fire/编号为 c11#~c30#的样品: 无解体、无着火现象				
	试验样品在试验中和试验后 <b>7</b> 天内,应无解体和无着火现象发生。	The data is shown in Table 4./数据见表 4				

	Table1: T1~T5 / 表 1. 试验 1~试验 5											
Sample No.	Mass prior to		OCV prior to test /试	Test T.1: simula 试验 T.1:	tion/	Test T.2: Th 试验 T.2: ;		Test T.3: V 试验 T.3		Test T.4: S 试验 T.4:		Test T.5: External Short Circuit/ 试验 T.5 外部 短路
样品号	验前质 量(g)	验前电 压(V)	Mass Loss(%) 质量损失(%)	OCV Retention Ratio(%) 电压保留比 (%)	Mass Loss(%) 质量损失(%)	OCV Retention Ratio(%) 电压保留比 (%)	Mass Loss(%) 质量损失(%)	OCV Retention Ratio(%) 电压保留比 (%)	Mass Loss(%) 质量损失(%)	OCV Retention Ratio(%) 电压保留比 (%)	Temp. (℃) 温度 (℃)	
b1#	93,049	4,173	0,003	99,98	0,020	99,26	0,000	99,98	0,000	100,00	57,3	
b2#	93,257	4,174	0,003	100,00	0,018	99,26	0,000	99,98	0,000	100,00	57,5	
b3#	93,133	4,169	0,003	99,98	0,020	99,30	0,000	100,00	0,000	100,00	57,2	
b4#	92,882	4,170	0,004	100,00	0,019	99,28	0,000	100,00	0,000	100,00	57,0	
b5#	93,201	4,165	0,004	100,00	0,020	99,33	0,000	100,00	0,000	100,00	57,6	
b6#	93,084	4,172	0,003	99,98	0,020	99,23	0,000	99,98	0,000	100,00	57,1	
b7#	93,298	4,168	0,003	100,00	0,018	99,38	0,000	99,98	0,000	100,00	56,9	
b8#	93,147	4,170	0,002	100,00	0,018	99,28	0,000	100,00	0,000	100,00	57,8	

Ref. No.:RZUN2023-2404 Pages 13 of 14 Pages

	Table2: Crush /表 2:挤压										
Test T.6: Crush/试 验 T.6:挤压	Sample No. 样品号	c1#	c2#	c3#	c4#	c5#	c6#	c7#	c8#	c9#	c10#
	OCV prior to test / 试验前电压(V)	3,824	3,827	3,827	3,827	3,825	3,824	3,824	3,827	3,826	3,827
	Temp. (℃) 温度 (℃)	24,3	25,1	24,6	25,5	24,9	23,8	24,4	25,3	25,6	24,7

Table3: Overcharge Test of batteries/ 表 3 过度充电										
Test T.7: Overcharg e /试验 T.7: 过度充 电	Sample No. 样品号	b1#	b2#	b3#	b4#	b5#	b6#	b7#	b8#	
	OCV prior to test /试 验前电压(V)	4,140	4,142	4,139	4,140	4,137	4,138	4,141	4,140	

Table 4: Forced discharge / 表 4. 强制放电											
Test T.8: Forced discharge / 试验 T.8: 强制放电	Sample No. 样品号	c11#	c12#	c13#	c14#	c15#	c16#	c17#	c18#	c19#	c20#
	OCV prior to test / 试验前电压(V)	3,386	3,390	3,389	3,390	3,385	3,391	3,389	3,389	3,386	3,388
	Sample No. 样品号	c21#	c22#	c23#	c24#	c25#	c26#	c27#	c28#	c29#	c30#
	OCV prior to test / 试验前电压(V)	3,387	3,390	3,383	3,386	3,393	3,390	3,389	3,390	3,386	3,384

### 注意事项 Important

1. 报告无检测单位印章无效。

The test report is invalid without the seal of CVC.

- 2. 未经本试验室书面同意,不得部分地复制本报告。
  Nobody is allowed to photocopy or partly photocopy this test report without written permission of CVC.
- 3. 本报告无批准人、审核人及检测人签名无效。
  The test report is invalid without the signatures of Ratifier, Reviewer and Testing engineer.
- 4. 本报告涂改无效。

The test report is invalid if altered,

- 5. 对检测报告若有异议,应于收到报告之日起十五天内向检测单位提出。 Objections to the test report must be submitted to CVC within 15 days.
- 6. 本报告仅对送检样品负责。

The test report is valid for the tested samples only.

7. 判定栏中"-"表示"不需要判定","P"表示"通过","F"表示"不通过", "N/A"表示"不适用"。

As for the Verdict, "-" means "no need for judgement", "P" means "pass", "F" means "fail" and "N/A" means "not applicable".

\*\*报告中未加 CMA 标志时,检测数据和结果仅供科研、教学或内部质量控制之用。\*\*
The test data and test results given in this test report should only be used for purposes of scientific research, teaching and internal quality control when the CMA symbol is not presented.

地 址: 广东省广州市科学城开泰大道天泰一路3号

广东省广州市黄埔区光谱东路 179 号百事高智慧园 D 栋 (测试地点)

Lab Address: No.3, Tiantai 1st Road, Kaitai Avenue, Science City, Guangzhou, Guangdong, China. Testing Location: Building D, BASIGO INTELLIGENT, No.179, Guangpu East Road, Huangpu District, Guangzhou, P. R. China.

http://www.cvc.org.cn