


## MILWAUKEE TOOL

Milwaukee Electric Tool Corporation
BROOKFIELD, WI 53005
USA
Tel: +1 (262) 781-3600 • Fax: +1 (262) 790-6333

Milwaukee Asia Office
29/F, Tower 2, Kowloon Commerce Centre,
51 Kwai Cheong Road, Kwai Chung, Hong Kong
Tel: +852-2492-2181 • Fax: +852-2490-4778

Distributed by:

30/8/2023

All data incl. service and warranty conditions as well as product range are subject to change without notice.
Pictures not binding. No liability for printing errors or mistakes. © 2023 Milwaukee Electric Tool Corporation.
All trademarks are owned by Techtronic Cordless GP unless otherwise stated.

www.milwaukeetool.asia

Milwaukee™


# M12 FUEL™

DRIVEN TO OUTPERFORM.™



**REDLINK PLUS™**
**INTELLIGENCE**



**POWERSTATE™**
**BRUSHLESS MOTOR**




**REDLITHIUM™**
**BATTERY PACK**

M12 FJS
**M12 FUEL JIG SAW**

**FASTER**
BLADE SPEED UNDERLOAD

MORE
**CONTROL**
IN MORE ORIENTATIONS

MAXIMUM
CUT LINE
**VISIBILITY**

# DRIVEN TO OUTPERFORM.

M12 FUEL is engineered for the most demanding tradesmen in the world. M12 FUEL delivers unrivaled performance in a compact structure and features three MILWAUKEE exclusive innovations - the POWERSTATE Brushless Motor, REDLITHIUM Battery Pack and REDLINK PLUS Intelligence Hardware and Software - that deliver unmatched power, run-time and durability.

M12 FUEL™



**ON/OFF CUT LINE BLOWER**
Integrated blower clears cut line of debris; turn off when using dust extraction



**SPEED DIAL**
Adjust speeds between 800 - 3,000 SPM

**POWERSTATE™ BRUSHLESS MOTOR**
Generates the power to cut hardwoods and metals under load

**ERGONOMIC BARREL GRIP DESIGN**
Delivers more control and enhanced maneuverability





**ON/OFF LED LIGHT**
Illuminates workpiece; turn off during inverted use

**ON-BOARD HEX WRENCH**
Quick bevel adjustments

**BEVEL ANGLE**
Bevel detents at 0°, 15°, 30°, and 45°

**ORBITAL CUTTING ACTION**
5 adjustment levels offer greater cut versatility in-application



**ON-BOARD BLADE STORAGE**
Conveniently store additional T-Shank blades

**SHOE GUARD**
Protects your workpiece





**TOOL-ONLY**
M12 FJS Contains: Includes: M12 Fuel Jig Saw, Dust Cover, Splinter Guard, Dust Extraction Tube, Shoe Guard, Hex Wrench and T-Shank Jig Saw Blade T144D.

Batteries and Charger Not Included.



## FASTER BLADE SPEED UNDERLOAD




- Faster blade speed under load
- To deliver clean, accurate, & quick cuts in hardwoods.

## MORE IN MORE ORIENTATIONS CONTROL




- Compact barrel grip tool design delivers
- More control in more orientations

## MAXIMUM CUT LINE VISIBILITY




- Integrated dust blower and led light delivers maximum cut line visibility in all orientations and site conditions



## SPECIFICATIONS

| DESCRIPTION | SPECIFICATIONS |
|---|---|
| SPM | 800-3000 |
| Stroke Length | 22.2mm |
| Blade type | T-shank |
| Speed Modes | 5+Auto |
| Orbital Settings | 5 |
| Cut Line Blower | Yes, On/Off |

| DESCRIPTION | SPECIFICATIONS |
|---|---|
| LED Light | Yes, On/Off |
| Max Bevel Capacity | 45° |
| Width (Tool-Only) | 74mm |
| Height (Tool-Only) | 183mm |
| Length (Tool-Only) | 226mm |
| Weight (Tool-Only) | 1.54 kg |