
COMPLIANT



Vishay High Power Products

Schottky Rectifier, 3.0 A



PRODUCT SUMMARY			
I _{F(AV)}	3.0 A		
V_{R}	15 V		
I _{RM}	50 mA at 100 °C		

FEATURES

- 125 °C T_J operation (V_R < 5 V)
- · Optimized for OR-ing applications
- Ultralow forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Compliant to RoHS directive 2002/95/EC
- · Designed and qualified for industrial level

DESCRIPTION

The 30BQ015PbF surface mount Schottky rectifier has been designed for applications requiring low forward drop and very small foot prints on PC boards. The proprietary barrier technology allows for reliable operation up to 125 °C junction temperature. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS				
SYMBOL	CHARACTERISTICS	VALUES	UNITS	
I _{F(AV)}	Rectangular waveform	3.0	A	
V _{RRM}		15	V	
I _{FSM}	t _p = 5 μs sine	650	A	
V _F	1.0 Apk, T _J = 75 °C	0.30	V	
T _J	Range	- 55 to 125	°C	

VOLTAGE RATINGS				
PARAMETER	SYMBOL	30BQ015PbF	UNITS	
Maximum DC reverse voltage	V _R	15	V	
Maximum working peak reverse voltage	V_{RWM}	25	V	

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
M		50 % duty cycle at T _L = 83 °C, rectangular waveform		3.0	
Maximum average forward current	Maximum average forward current I _{F(AV)}		50 % duty cycle at T _L = 78 °C, rectangular waveform		
Maximum peak one cycle non-repetitive surge current		5 μs sine or 3 μs rect. pulse	Following any rated load condition and with	650	Α
	10 ms sine or 6 ms rect. pulse	rated V _{RRM} applied	75		
Non-repetitive avalanche energy	E _{AS}	T _J = 25 °C, I _{AS} = 0.5 A, L = 12 mH		1.5	mJ
Repetitive avalanche current	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T_J maximum $V_A = 1.5$ x V_B typical		0.5	Α

Document Number: 94178 Revision: 02-Jul-09

30BQ015PbF

Vishay High Power Products Schottky Rectifier, 3.0 A



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum forward voltage drop	V _{FM} ⁽¹⁾	3 A	T _J = 25 °C	0.35	V
		6 A		0.40	
		3 A	T _J = 75 °C	0.30	
		6 A		0.35	
Maximum reverse leakage current	I _{RM} ⁽¹⁾	T _J = 25 °C	V _R = Rated V _R	4	- mA
		T _J = 100 °C		50	
Maximum junction capacitance	C _T	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		1120	pF
Typical series inductance	L _S	Measured lead to lead 5 mm from package body		3.0	nH
Maximum voltage rate of change	dV/dt	Rated V _R		10 000	V/µs

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction temperature range	T _J ⁽¹⁾		- 55 to 125	°C
Maximum storage temperature range	T _{Stg}		- 55 to 150	10
Maximum thermal resistance, junction to lead	R _{thJL} (2)	DC operation	12	°C/W
Maximum thermal resistance, junction to ambient	R _{thJA}	DC operation	46	C/VV
Approximate weight			0.24	g
Approximate weight			0.008	OZ.
Marking device		Case style SMC (similar to DO-214AB)	V3	BC

Notes

Document Number: 94178 Revision: 02-Jul-09

 $[\]frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}} \quad \text{thermal runaway condition for a diode on its own heatsink}$

⁽²⁾ Mounted 1" square PCB



Schottky Rectifier, 3.0 A Vishay High Power Products




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)

Vishay High Power Products Schottky Rectifier, 3.0 A






Fig. 5 - Maximum Average Forward Current vs. Allowable Lead Temperature




Fig. 6 - Maximum Average Forward Dissipation vs.
Average Forward Current




Fig. 7 - Maximum Peak Surge Forward Current vs.
Pulse Duration

Note


(1) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$; $Pd = Forward power loss = I_{F(AV)} \times V_{FM} at (I_{F(AV)}/D)$ (see fig. 6); $Pd_{REV} = Inverse power loss = V_{R1} \times I_R (1 - D)$; I_R at $V_{R1} = 80 \%$ rated V_R



Schottky Rectifier, 3.0 A Vishay High Power Products

ORDERING INFORMATION TABLE

Device code



1 - Current rating

2 - B = Single lead diode

- Q = Schottky "Q" series

Voltage rating (015 = 15 V)

• None = Box (1000 pieces)

• TR = Tape and reel (3000 pieces)

6 - PbF = Lead (Pb)-free

LINKS TO RELATED DOCUMENTS				
Dimensions <u>www.vishay.com/doc?95023</u>				
Part marking information	www.vishay.com/doc?95029			
Packaging information	www.vishay.com/doc?95034			

Document Number: 94178 Revision: 02-Jul-09



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com