

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5039084100](#)
Status: **Active**
Overview: [LVDS FFC Connectors](#)
Description: 0.50mm Pitch Easy-On One-Touch FFC Connector for LVDS, Non-ZIF, with Side Locks, Bottom Contact Style, 3.75mm Height, Right-Angle, Surface Mount, 41 Circuits

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-503908-001-001 \(PDF\)](#)
[Packaging Specification 5039089200-200 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series [503908](#)
Overview [LVDS FFC Connectors](#)
Product Name Easy-On
UPC 887191532899

Physical

Actuator Type Non-ZIF
Circuits (Loaded) 41
Circuits (maximum) 41
Color - Resin Black
Contact Position Bottom
Durability (mating cycles max) 20
Mated Height 3.75mm
Material - Metal Copper Alloy
Material - Plating Mating Gold over Nickel
Material - Plating Termination Gold over Nickel
Material - Resin Liquid Crystal Polymer
Net Weight 790.942/mg
Number of Rows 1
Orientation Right Angle
PCB Mounting Surface Mount
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.50mm
Plating min - Mating 0.102µm
Plating min - Termination 0.051µm
Polarized to PCB Yes
Stackable No
Temperature Range - Operating -20° to +85°C
Wire/Cable Type FFC only

Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

[Packaging Specification 5039089200-200](#)
[Product Specification PS-503908-001-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[503908](#) Series

Use With

LVDS Cable [15023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

503908-4100