SAFETY DATA SHEET

RS PRO Corrosion Inhibitor

Stock No: 894-6941

This Safety Data Sheet contains information concerning the potential risks to those involved in handling, transporting and working with the material, as well as describing potential risks to the consumer and the environment. This information must be made available to those who may come into contact with the material or are responsible for the use of the material. This Safety Data Sheet is prepared in accordance with formatting described in the REACH Regulation (EC) No 1907/2006, and described in CLP Regulation (EC) No 1272/2008.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

CM100 Inhibitor

1.2 Relevant identified uses of the substance or mixture and uses advised against

Corrosion inhibitor

1.3 Details of the supplier of the safety data sheet

Calmag (Yorkshire) Ltd Riverview Buildings Bradford Road Riddlesden Keighley West Yorkshire BD20 5LN

Tel: 01535 210320 Fax: 01535 210321

Email: sales@calmagltd.com
Web: www.calmagltd.com

1.4 Emergency telephone number

Tel: 01535 210320 (9.00am – 5.00pm Mon-Fri except Public Holidays)

PRC

SECTION 2: Hazards Identification

2.1 Classification of the substance or mixture

Not classified as hazardous

2.2 Label elements

No labelling required

2.3 Other hazards

May cause irritation on prolonged exposure.

SECTION 3: Composition

3.1 Substances

Not applicable

3.2 Mixtures

An aqueous mixture which contains no components considered hazardous above thresholds of concern.

SECTION 4: First Aid Measures

4.1 Description of first aid measures

EYE CONTACT: Wash thoroughly with water for several minutes, holding the eyelids apart. Seek medical attention if irritation persists.

INHALATION: Remove from exposure. If breathing becomes difficult call a doctor.

SKIN CONTACT: Wash off with soap and water. Seek medical attention if irritation persists..

INGESTION: If swallowed, rinse mouth with water. Do NOT induce vomiting. Seek medical attention.

4.2 Most important symptoms and effects, both acute and delayed

EYES: Not expected to result in adverse effects

INHALATION: Not expected to result in adverse effects

SKIN: Not expected to result in adverse effects

INGESTION: Not expected to result in adverse effects

4.3 Indication of any immediate medical attention and special treatments needed

Symptomatic treatment as required.

SECTION 5: Firefighting Measures

5.1 Extinguishing media

Not flammable. Use extinguishing media appropriate to surrounding conditions.

5.2 Special hazards arising from the substance or mixture

Oxides of carbon, nitrogen and metal.

5.3 Advice for fire fighters

Fire fighters should wear protective clothing and breathing apparatus as appropriate.

SECTION 6: Accidental Release Measures

6.1 Personal precautions, protective equipment and emergency procedures

Wear protective clothing including gloves and eye protection. Open doors and windows to ensure good ventilation.

6.2 Environmental precautions

Uncontrolled discharges into water courses must be immediately alerted to the relevant authorities.

6.3 Methods and materials for containment and clearing up

Small spills (<1 litre) may be washed to foul drain with copious quantities of water. Dilute with water and mop up.

Large spills (> 1 litre) should be covered with a suitable absorbent, e.g. sand, earth or spill granules and collected for disposal. Wash spill area thoroughly with soapy water.

Contain the spillage using bunding.

6.4 References to other sections

See section 8 and 13 for further advice.

SECTION 7: Handling and Storage

7.1 Precautions for safe handling

Avoid contact with skin and eyes. Do not inhale vapours, mists or sprays.

7.2 Conditions for safe storage, including any incompatibilities

Keep containers tightly closed and in a cool, well ventilated area. Keep only in original container.

7.3 Specific end uses(s)

No special precautions.

Page 2 of 5

SECTION 8. Exposure Controls/Personal Protection

8.1 Control parameters

No exposure limits available for the components of the mixture.

8.2 Exposure controls

None usually required during normal handling. Normal chemical handling procedures should be observed. Do not eat, drink or smoke when handling this product. Wash thoroughly after handling,

Respiratory protection

Not usually required. Use in well ventilated areas and avoid formation of spray or aerosols.

Hand Protection

Wear protective gloves if prolonged skin contact is likely.

Eye protection

Safety glasses with side shields or goggles should be worn if there is a risk of splashing eyes.

Skin protection

Coveralls recommended. These should be changed after use or if contaminated. Wash before re-use.

Environmental exposure controls

Precautions should be taken to avoid accidental release to water courses.

SECTION 9: Physical and Chemical Properties

9.1 Information on basic physical and chemical properties

Appearance: Yellow liquid Odour: Odourless Odour threshold: No data 8.2(8.0 - 8.5)pH: Melting point: Similar to water **Boiling point:** Similar to water Flashpoint: Not flammable Evaporation rate: Similar to water Flammability (solids/gases): Not applicable Upper/lower flammability limits: Not flammable Vapour pressure: Similar to water Vapour density Similar to water

Specific gravity Approximately 1.1 g/cm³ **Solubility in water:** Completely soluble in water

Solubility in other solvents: No data

Partition coefficient (log Kow) -No data

Autoignition temperature Not flammable

Decomposition temperature No data

Viscosity No data

Explosive propertiesOxidising properties
Not classified as explosive
Not classified as oxidising.

9.2 Other information

None

SECTION 10: Stability and Reactivity

10.1 Reactivity

Not considered to be reactive.

10.2 Chemical stability

Stable under normal conditions.

Page 3 of 5

10.3 Possibility of hazardous reactions

Under normal conditions of storage and use, hazardous reactions will not occur.

10.4 Conditions to avoid

Excessive heat.

10.5 Incompatible materials

None.

10.6 Hazardous decomposition products

None expected under normal conditions of use.

SECTION 11: Toxicological Information

11.1 Information on toxicological effects

This product has not been tested. Judgements on the expected toxicity of this product have been made based upon consideration of its major components.

- (a) acute toxicity Contains no components known to be acutely toxic above thresholds of concern.
- **(b) skin corrosion/irritation** Contains no components known to be corrosive or irritant above thresholds of concern.
- **(c) serious eye damage/irritation** Contains no components known to be corrosive or irritant above thresholds of concern.
- **(d) respiratory/skin sensitisation** Contains no components known to be sensitising above thresholds of concern.
- **(e) germ cell mutagenicity** Contains no components known to be germ cell mutagens above thresholds of concern.
- **(f) carcinogenicity** Contains no components known to be carcinogens above thresholds of concern.
- **(g) reproductive toxicity** Contains no components known to be reproductive toxins above thresholds of concern.
- **(h) STOT-single exposure** Contains no components known to cause specific target organ toxicity above thresholds of concern.
- (i) STOT-repeated exposure Contains no components known to cause specific target organ toxicity above thresholds of concern.
- (i) aspiration hazard The product is not expected to be an aspiration hazard.

SECTION 12: Ecological Information

This product has not been tested. Judgements on the expected toxicity of this product have been made based upon consideration of its major components.

12.1 Toxicity

Not expected to be toxic in the environment.

12.2 Persistence and degradability

Part of the mixture is biodegradable.

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

All components are readily soluble in water and if released into soil will be mobile in the environment.

12.5 Results of PBT and vPvB assessment

None of the components are known to be PBT or vPvB.

12.6 Other adverse effects

None known.

Page 4 of 5

14.1

SECTION 13: Disposal Considerations

13.1 Waste treatment methods

Dispose of waste and residues in accordance with local authority regulations. Recover and recycle product if possible.

Empty containers should be thoroughly rinsed with copious amounts of clean water. The spent container may be disposed of with recycled household refuse providing it has been rinsed.

SECTION 14: Transport Information

UN Number

Not classified as hazardous for transport.

14.2	UN Proper shipping name	Not applicable			
14.3	Transport hazard class(es)	Not applicable			
14.4	Packing group Not a	applicable			
14.5	Environmental hazards Not a	applicable			
14.6	Special precautions for user	None			
14.7	Transport in bulk according to	Annex II of MARPOL 73/78 and the IBC Code	Not	transported	in
bulk	· · · · · · · · · · · · · · · · · · ·				

Not applicable

SECTION 15: Regulatory Information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture All components are listed as existing substances in Europe

15.2 Chemical Safety Assessment

A Chemical Safety Assessment has not been carried out for this product.

SECTION 16: Other Information

Revision information: Updated to remove references to DSD and DPD classification and labelling.

List of Abbreviations used in this SDS:

	<u> </u>		•
CAS	Chemical	Abstracts	Service

CLP Classification, Labelling and Packaging Regulation (EC) no 1272/2008

DSD Dangerous Substances Directive 67/548/EEC

DPD Dangerous Preparations Directive 1999/45/EC

EC European Commnity/Commission

PBT Persistent, Bioaccumulative and Toxic

REACH Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) no 1907/2006

vPvB very Persistent, very Bioaccumulative

R Phrases and H Statements used in Section 2 and/or 3

None

References:

Suppliers safety data sheet.

ECHA Classification and Labelling Inventory

Method used for classification of mixtures:

Ingredient based approaches and expert judgment

Training requirements for workers

No special training requirements.