




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Natural**

Number of Positions: **36**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Holder
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	36
---------------------	----

Body Features

Primary Product Color	Natural
-----------------------	---------

Housing Features

Centerline (Pitch)	1.5 mm[.059 in]
--------------------	-----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

--	--



Packaging Method	Box
Packaging Quantity	400

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 3-292229-6
1.5 MINI CT D/R SMT 36P V ONTA



TE Part # 8-292216-6
MINI CT D/R RELAY 36P V BLUE



TE Part # 3-292216-6
MINI CT D/R RELAY 36P V NAT



TE Part # CAT-AM7053-C7671
Mini Common Termination Contacts



TE Part # 1-353293-8
MINI CT MT REC ASSY 18P GRAY

TE Part # 3-292208-6
MINI CT D/R DIP 36P V NAT

TE Part # 3-292262-6
DBL ROW (H) DIP TYPE WITH BOAR

TE Part # 1-353293-3
MINI CT MT REC ASSY 13P GRAY

Also in the Series | AMP Mini CT

Connector Contacts(4)

Connector Hardware(10)

PCB Headers & Receptacles(332)

Wire-to-Board Connector Assemblies & Housings(172)

Wire-to-Board Headers & Receptacles (332)

Customers Also Bought

TE Part #1-292254-0
CT RELAY HDR ASSY 10P NAT

TE Part #CAT-AM7053-H8172
Mini Common Termination (CT) Housings

TE Part #3-353294-2
AMP MINI D/R HDR HSG 32P NATU

TE Part #292215-6
MINI CT SGL RELAY 6P NAT

TE Part #2-173983-4
AMP CT MT AMP-IN HDR-H YEL 4P

TE Part #2-353294-8
AMP MINI D/R HDR HSG 28P NATU

TE Part #1-292215-2
MINI CT SGL RELAY 12P NAT

TE Part #1-179228-2
CT CRIMP-2 REC HSG 12P NATURAL



TE Part #292254-9
CT RELAY HDR ASSY 9P NAT

Documents

Product Drawings

AMP MINI D/R HDR HSG 36P NATU

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_3-353294-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_3-353294-6_E.3d_stp.zip

English

Customer View Model

ENG_CVM_3-353294-6_E.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English