

Product data sheet

Specifications



Repacked, cable outlet, Ovalis, 16A,
dia 6-12 mm, white

S260633W



This repacked option saves 0.213 over the
standard condition

Main

Range of product	Ovalis
Product or component type	Cable outlet
Device presentation	Complete product
Product specific application	Exit wire for electrical heating
Colour tint	White (RAL 9003)
Type of packing	Paint cover
Quantity per set	5 pieces
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Rated current	16 A
fixing mode	By screws
Surface finish	Satin
Connections - terminals	Screw
Number of loop terminals	2
shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...1 x 2.5 mm ² for rigid cable(s) 1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable outer diameter	6...12 mm
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	54 mm
Embedding depth	26.7 mm
Product weight	0.036 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1 UTE C 61-392
IK degree of protection	IK04
IP degree of protection	IP33
Environmental characteristic	Window-cleaning fluid Alcohol Bleach UV resistant Oil Petrol Acetone Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	8.400 cm
Package 1 Length	8.900 cm
Package 1 Weight	33.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	13.200 cm
Package 2 Width	12.800 cm
Package 2 Length	19.000 cm
Package 2 Weight	387.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	180
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	7.720 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.2 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

59bc1733-7007-4ba6-bfd5-f7904c7d9a13

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins