

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Primary-switched TRIO POWER power supply in IP67 die-cast housing, M12 circular connector, input: 1-phase, 5-pos. output: 24 V DC/10 A, static boost: up to 12.5 A (continuous)



Product description

The robust power supplies with IP67 degree of protection are ideally suited for decentral supply in the field. The weather-resistant cast-aluminum housing protects the devices against dust and water. This enables the power supplies to ensure high system availability even in harsh ambient conditions. The different device connections provide flexibility during mounting.

Your advantages

- Direct installation at the load in the field reduces cable lengths and saves space in the control cabinet
- The robust cast-aluminum housing ensures high system availability with resistance to extreme ambient conditions (temperature, dust, and water)
- High shock and vibration resistance, plus high electric strength
- Improved diagnostic options in the field with DC OK LED

Commercial data

Item number	1395808
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CMP
Product key	CMPF13
GTIN	4063151779092
Weight per piece (including packing)	1,703 g
Weight per piece (excluding packing)	6 g
Customs tariff number	85044095
Country of origin	CN

Technical data

Input data

AC operation

Supply system configuration	Star network (TN, TT, IT (PE))
Nominal input voltage range	120 V AC ... 240 V AC
Input voltage range	120 V AC ... 240 V AC $\pm 10\%$
Switch-on voltage	$> 85\text{ V AC}$
Shut-down voltage	$< 85\text{ V AC}$
Electric strength, max.	$\leq 300\text{ V AC } 15\text{ s}$
Typical national grid voltage	120 V AC
	230 V AC
Voltage type of supply voltage	AC
Inrush current	$\leq 25\text{ A (typical)}$
Inrush current integral (I^2t)	$< 0.5\text{ A}^2\text{s}$
Inrush current limitation	typ. 25 A (after 1 ms)
AC frequency range	50 Hz ... 60 Hz $\pm 10\%$
Frequency range (f_N)	50 Hz ... 60 Hz $\pm 10\%$
Mains buffering time	$> 17\text{ ms (120 V AC)}$
	$> 17\text{ ms (230 V AC)}$
Current consumption	2.3 A (120 V AC)
	1.2 A (240 V AC)
Nominal power consumption	285 VA
Protective circuit	Transient surge protection; Varistor
Switch-on time	$< 1\text{ s}$
Input fuse	6.3 A (internal (device protection))
Recommended breaker for input protection	6 A ... 16 A (US/CAN: branch circuit protection $\leq \text{UL}\downarrow\text{A}$) (Characteristic B, C, D, K or comparable)
Discharge current to PE	$< 3.5\text{ mA}$

Output data

Efficiency	typ. 90 % (120 V AC)
	typ. 92 % (230 V AC)
Nominal output voltage	24 V DC $\pm 1\%$
Nominal output current (I_N)	10 A
Static Boost ($I_{\text{Stat.Boost}}$)	12.5 A ($U_N \geq \text{UL}\downarrow\text{V AC}$)
Derating static boost	$> 40\text{ }^\circ\text{C} \dots 50\text{ }^\circ\text{C } 1\text{ }^\circ\text{C}/\text{K}$ $> 50\text{ }^\circ\text{C} \dots 60\text{ }^\circ\text{C } 0.22\text{ }^\circ\text{C}/\text{K}$ ($U_N \geq \text{UL}\downarrow\text{V AC}$, $P_{\text{Stat.Boost}} = P_N \times 1.25$)
Dynamic Boost ($I_{\text{Dyn.Boost}}$)	15 A (5 s)
Derating	$> 40\text{ }^\circ\text{C} \dots 50\text{ }^\circ\text{C } (1\text{ }^\circ\text{C} / \text{K})$
Feedback voltage resistance	$\leq 35\text{ V DC}$
Protection against overvoltage at the output (OVP)	$\leq 30\text{ V DC}$
	$< 1\%$ (change in load, static 10 % ... 90 %)

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Control deviation	< 3 % (Dynamic load change 10 % ... 90 %, 10 Hz)
	< 0.1 % (change in input voltage ± 10 %)
Residual ripple	≤ 10 mV _{PP}
Short-circuit-proof	yes
Output power	240 W
	300 W
	360 W (5 s)
Maximum no-load power dissipation	< 2 W (120 V AC)
	< 2 W (230 V AC)
Power loss nominal load max.	< 25 W (120 V AC)
	< 21 W (230 V AC)
Rise time	≤ 12 ms (U_{OUT} (10 % ... 90 %))
Connection in parallel	yes, for redundancy and increased capacity
Connection in series	yes

Signal relay 13/14

Default	closed
Digital	30 V AC 30 V DC 100 mA

Connection data

Input

Connection method	M12 circular connector
Coding	S
Type of locking	M12 screw locking
Number of positions	3

Output

Connection method	M12 circular connector
Coding	L
Type of locking	M12 screw locking
Number of positions	5

Signal

Connection method	M12 circular connector
Coding	A
Type of locking	M12
Number of positions	5

Signaling

Types of signaling	LED
	Floating signal contact
Status display	2 x LED (green)

Signal output: LED status indicator

Signalization designation	AC OK
---------------------------	-------

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Status display	LED
Color	green
AC OK	$AC_{In} > 0.45 \times AC_N$ ($AC_N = 108 \text{ V AC}$)

Signal output: LED status indicator

Signalization designation	DC OK
DC OK	$U_{OUT} > 0.9 \times U_N$ ($U_N = 24 \text{ V DC}$)

Electrical properties

Number of phases	1.00
Insulation voltage input/output	3 kV AC (type test)
	1.5 kV AC (routine test)

Product properties

Product type	Power supply
Product family	TRIO POWER
MTBF (IEC 61709, SN 29500)	> 850000 h (25 °C)
	> 460000 h (40 °C)
	> 190000 h (60 °C)

Insulation characteristics

Protection class	I
Pollution degree	2 (IEC 61010-1)

Dimensions

Item dimensions

Width	136 mm
Height	240 mm
Depth	53 mm

Drill hole

Diameter	5.6 mm
----------	--------

Installation dimensions

Installation distance right/left	10 mm / 10 mm
Installation distance top/bottom	0 mm / 100 mm

Mounting

Mounting type	Panel mounting
Assembly note	Alignable: 20 mm horizontally, 50 mm vertically above, 100 mm vertically below
With protective coating	no

Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Metal

Type of housing	Aluminum (AlMg3)
-----------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (start-up type tested)	-40 °C
Maximum altitude	≤ 4000 m (> 2000 m, Derating: 10 %/1000 m)
Climatic class	4K26 (EN 60721-3-4)
Max. permissible relative humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Permissible humidity (operation)	≤ 100 % (at 25 °C, non-condensing)
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6) 15 Hz ... 150 Hz, 4g, 90 min.

Standards and regulations

Overvoltage category

EN 61010-1	III (≤ 2000 m)
	II (≤ 4000 m)

Electrical safety

Standard designation	Electrical safety
Standards/specifications	IEC 61010-1

Protective extra-low voltage

Standard designation	Protective extra-low voltage
Standards/specifications	IEC 61010-1 (SELV)
	IEC 61010-2-201 (PELV)

Safe isolation

Standard designation	Safe isolation
----------------------	----------------

Low-voltage power supplies, DC output

Standard designation	Low-voltage power supplies, DC output
Standards/specifications	EN 61204-3

Safety requirements for electrical equipment for measurement, control, and laboratory use

Standard designation	Safety requirements for electrical equipment for measurement, control, and laboratory use
Standards/specifications	IEC 61010-1

Limit values for harmonic currents

Standard designation	Limit values for harmonic currents
Standards/specifications	EN 61000-3-2

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Degrees of protection provided by enclosures (IP code)

Standard designation	Degrees of protection provided by enclosures (IP code)
Standards/specifications	EN/IEC 60529

Approvals

UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

UL

Identification	UL/C-UL Listed UL 61010-2-201
----------------	-------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Interference emission	Interference emission in accordance with EN 61000-6-3 (residential and commercial) and EN 61000-6-4 (industrial)
Noise immunity	Immunity in accordance with EN 61000-6-1 (residential), EN 61000-6-2 (industrial)

Conducted noise emission

Standards/regulations (Higher requirements in practice (covered))	EN 55016
	EN 61000-6-3 (Class B)
Noise emission	EN 55011 (EN 55022)
Noise emission ()	EN 55016
	EN 61000-6-3 (Class B)

Harmonic currents

Standards/regulations	EN 61000-3-2
	EN 61000-3-2 (Class A)

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	6 kV (Test Level 3)
Comments	Criterion A

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 2 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	2 GHz ... 6 GHz
Test field strength	10 V/m (Test Level 3)

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Input	4 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Signal	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion A
Surge voltage load (surge)	
Standards/regulations	EN 61000-4-5
Surge voltage load (surge)	
Input	1 kV (Test Level 1 - symmetrical)
	2 kV (Test Level 1 - asymmetrical)
Output	0.5 kV (Test Level 1 - symmetrical)
	0.5 kV (Test Level 1 - asymmetrical)
Signal	1 kV (Test Level 2 - asymmetrical)
Comments	Criterion B
Conducted interference	
Standards/regulations	EN 61000-4-6
Conducted interference	
Input/Output	asymmetrical
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)
Voltage dips	
Standards/regulations	EN 61000-4-11
Voltage	230 V AC
Frequency	50 Hz
Voltage dip	70 %
Number of periods	25 periods
Comments	Criterion A
Voltage dip	40 %
Number of periods	10 periods
Comments	Criterion A
Voltage dip	0 %
Number of periods	1 period
Comments	Criterion A
Emitted interference	
Standards/regulations	EN 61000-6-3

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>


Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.
Criterion C	Temporary adverse effects on the operating behavior, which the device corrects automatically or which can be restored by actuating the operating elements.


Drawings

Block diagram




Block diagram


Diagram




Output current/installation altitude



Power factor



Efficiency



Input current/output current

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1395808>



cULus Listed

Approval ID: FILE E 123528



IECEE CB Scheme

Approval ID: DK-135371-A1-UL

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Classifications

ECLASS

ECLASS-11.0	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701

ETIM

ETIM 9.0	EC002540
----------	----------

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bec6d311-d138-4b08-862f-ce5c66fb6f8f

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

Accessories

SACC-M12FSS-2PEPL-CM SH - Power connector

1080227

<https://www.phoenixcontact.com/in/products/1080227>



Power connector, Power, 3-position, shielded, Socket straight M12, coding: S, Push-lock spring connection, knurl material: Brass, nickel-plated, external cable diameter 6 mm ... 11 mm

SAC-3P- 1,0-PUR/M12FSS PE - Power cable

1176479

<https://www.phoenixcontact.com/in/products/1176479>



Power cable, 3-position, PUR halogen-free, black, free cable end, on Socket straight M12, coding: S, cable length: 1 m, For alternating current up to 16 A/690 V

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

SACC-M12MSL-4PL-CM SH - Power connector

1080239

<https://www.phoenixcontact.com/in/products/1080239>



Power connector, Power, 4-position, shielded, Plug straight M12, coding: L, Push-lock spring connection, knurl material: Brass, nickel-plated, external cable diameter 6 mm ... 11 mm

SACC-M12MSL-4FEPL-CL - Power connector

1151368

<https://www.phoenixcontact.com/in/products/1151368>



Power connector, Power, 5-position, unshielded, Plug straight M12, coding: L, Push-lock spring connection, knurl material: Brass, nickel-plated, external cable diameter 8 mm ... 13 mm

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

SAC-5P-M12MSL/ 1,5-280 FE - Power cable

1414883

<https://www.phoenixcontact.com/in/products/1414883>



Power cable, 5-position, PUR halogen-free, gray RAL 7001, Plug straight M12, coding: L, on free cable end, cable length: 1.5 m, for direct current up to 16 A/63 V

SACC-M12FS-5PL M - Connector

1424652

<https://www.phoenixcontact.com/in/products/1424652>



Connector, Universal, 5-position, unshielded, Socket straight M12, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4 mm ... 8 mm

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

SAC-5P- 1,5-PUR/M12FS - Sensor/actuator cable

1669822

<https://www.phoenixcontact.com/in/products/1669822>



Sensor/actuator cable, 5-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 1.5 m

SAC-5P-M12MSL/3,0-280/FSL FE - Power cable

1425012

<https://www.phoenixcontact.com/in/products/1425012>



Power cable, 5-position, PUR halogen-free, gray RAL 7001, Plug straight M12, coding: L, on Socket straight M12, coding: L, cable length: 3 m, for direct current up to 16 A/63 V

TRIO-PS67/1AC/24DC/10/M12/5P - Power supply unit



1395808

<https://www.phoenixcontact.com/in/products/1395808>

SAC-5P-M12MSL/3,0-500/FSL FE - Power cable

1425016

<https://www.phoenixcontact.com/in/products/1425016>



Power cable, 5-position, PVC, gray RAL 7001, Plug straight M12, coding: L, on Socket straight M12, coding: L, cable length: 3 m, for direct current up to 16 A/63 V

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in