

SENCITY® OMNI-S stick antenna 1399.17.0232

SWA-1727/360/2/0/V

Description

Omni - directional multiband antenna for GSM 1800, GSM/PCS 1900, UMTS, LTE 2300, 2500 and 2600,
 Also WLAN IEEE 802.11 b/g WiFi 2400 to 2500 MHz
 Gain 2 dBi, vertical polarized antenna
 Ingress protection IP67 (IEC 60529)
 For outdoor and indoor applications
 Pole or wall mount



Product Configuration

Technical Data

Electrical Data

	Band 1
Frequency (MHz)	1710 - 2690
VSWR	1.8
Impedance (Ohm)	50
Gain (dBi)	2
3dB beamwidth (h) (°)	360
3dB beamwidth (v) (°)	65

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical

General Data

DC Grounding	Yes
IMD level	145 dBc at carrier power 2x 30dBm
Composite Power max (W)	25

Mechanical Data

Dimensions (mm)	120 x 22 (Height x Diameter)
Weight (kg)	0.3

INCLUDED MOUNTING MATERIAL: Bracket 9091.99.0173 and 2 metal-bands for mast-diameter 25mm - 101mm, all piece parts made of stainless steel

Environmental Data

Environmental conditions	outdoor
Operation temperature (°C)	-40 to 85
Storage temperature (°C)	-55 to 85
Transport temperature (°C)	-40 to 85
IP rating	IP67
RoHS 2011/65/EU	compliant
Lead-free soldered	yes
REACH 2006/1907/EC	compliant

LOW TEMPERATURE: IEC 60068-2-1 72h -55°C
 HIGH TEMPERATURE: IEC 60068-2-2 72h +85°C
 HUMIDITY: ETSI EN300-2-4 T4, 1E 144h 95%
 SALT SPRAY: EN 60068-2-11 / GB-T 10125 96h

SENCITY® OMNI-S stick antenna 1399.17.0232

MECHANICAL SHOCK: IEC 60721-3-4, 4M5

VIBRATION: IEC 60721-3-4 30 min/axis random 4M5

Material Data

Radome colour	RAL 9003 (signal white)
Radome material	Glass Fibre

Related Products

9091.99.0173 L - bracket for omni stick antennas

Related Documents

Mounting instruction	DOC-0000296554
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DOU-00285540
3D-model	DOC-0000684122

Additional Information

Mounting accessory included