

Multi Tool LXT®

DTM50

18V

Multi-tool for cutting, polishing, grout removal and other applications

A handy 18V LXT® multi-function tool for a variety of cutting and polishing applications in construction and renovation projects. The oscillating rate can be adjusted between 6 000 and 20 000 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Orbits per Minute	6000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,6 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	81 - 87 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding	≤ 2,5 m/s ²
Tool weight with battery	1,8 - 2,2 kg
Product Dimensions (L x W x H):	324 x 80 x 122 mm
Sound Power Level (L _{WA})	89 - 95 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Vibration Level, Cutting With Plunge Cut Saw Blade	10,0 m/s ²

User benefits

- Variable speed
- Soft start for smooth start-ups
- The rubber coating on the handle ensures a firm working grip
- Single LED job light illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing