

## Features

- WRAS approved
- Small and quiet in operation
- Minimum working pressure 0.15 bar
- Fits most tanks and cisterns
- Manufactured from 4-ton tensile strength engineering resin to high tolerances
- Available for side and bottom inlets
- Tail length 1 1/4 in (1/2 in Male BSP Thread)
- Removable, easily cleaned filter
- Pressure maximum 14 bar
- Stock no. 802-070 is side entry, Stock no. 802-086 is bottom entry

## RS PRO Tank & Cistern Float Valve, 1/2in

RS Stock No.: 802-070



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*The valve is manufactured from engineering resin with an impressive tensile strength of 4 tonnes, so you're assured a tough and hardwearing part. It features a removable filter that's easy to clean. It can be used at pressures between 0.15 bar and 14 bar. The tail is one-and-a-quarter inches long and has a half-inch male thread.*

## General Specifications

Connection Size	1/2 in
Maximum Working Pressure	14 bar