



Product data sheet

Power tools for trade & industry

Cordless Palm Router

PRO GKF 18V-8



Flagship 18V palm router: Maximum power and accessory compatibility with top-of-the-line features, for unrivalled versatility.

The most important data

Battery voltage	18.0 V
No-load speed	10,000 – 30,000 rpm
Compatible collet diameters	6 mm, 8 mm, 1/4"

Part Number 0 601 6C2 004

Technical data

Technical data

Battery voltage	18.0 V
No-load speed	10,000 – 30,000 rpm
Weight excl. battery	1.1 kg
Packaging dimensions (width x length x height)	360 x 444 x 254 mm
Compatible collet diameters	6 mm, 8 mm, 1/4"
BITURBO	No

Noise/vibration information

Total vibration values

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- The most compact height of any 18V palm router, for reduced top heaviness and excellent tool control
- Best-in-class dust collection and accessory compatibility, thanks to purpose-built surface and edge routing vacuum adaptors, and the markets broadest range of optional palm routing accessories
- Fine depth adjustment, hands-free spindle lock, and dual L.E.D lights to satisfy the most demanding professional's needs



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

