

FEATURES

- **Graphite material:** Provides excellent thermal conductivity and chemical resistance
- **Maximum operating pressure of 20000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 650°C:** Ideal for high-temperature environments
- **Rotary speed of 30 m/s:** Supports high-speed applications
- **12.5 mm section:** Ensures robust sealing capability

RS PRO 8m Graphite Gland & Valve Packing, 12.5mm Section

RS Stock No: 606-566



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland and valve packing is designed for sealing applications in high-pressure and high-temperature environments. Made from durable graphite, it offers excellent resistance to extreme conditions, making it ideal for industrial use. The packing ensures reliable sealing performance, reducing maintenance needs and enhancing operational efficiency.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	12.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------