

Main

Range compatibility	Lexium 28
Device short name	BCH2
Product or component type	Servo motor

Complementary

Maximum mechanical speed	3000 rpm
[Us] rated supply voltage	220 V 110 V
Network number of phases	Three phase Single phase
Continuous stall current	1.88 A
Continuous stall torque	2.86 N.M for LXM26D at 2.6 A, 220 V, single phase 2.86 N.M for LXM26D at 2.6 A, 220 V, three phase 2.86 N.M for LXM28... at 2.6 A, 220 V, single phase 2.86 N.M for LXM28... at 2.6 A, 220 V, three phase 2.86 N.m for LXM28... at 5.7 A, 110 V, single phase
Continuous power	300 W
Peak stall torque	8.59 N.M for LXM26D at 2.6 A, 220 V, single phase 8.59 N.M for LXM26D at 2.6 A, 220 V, three phase 8.59 N.M for LXM28... at 2.6 A, 220 V, single phase 8.59 N.M for LXM28... at 2.6 A, 220 V, three phase 8.59 N.m for LXM28... at 5.7 A, 110 V, single phase
Nominal output power	300 W for LXM26D at 2.6 A, 220 V, single phase 300 W for LXM26D at 2.6 A, 220 V, three phase 300 W for LXM28... at 2.6 A, 220 V, single phase 300 W for LXM28... at 2.6 A, 220 V, three phase 300 W for LXM28... at 5.7 A, 110 V, single phase
Nominal torque	2.86 N.M for LXM26D at 2.6 A, 220 V, single phase 2.86 N.M for LXM26D at 2.6 A, 220 V, three phase 2.86 N.M for LXM28... at 2.6 A, 220 V, single phase 2.86 N.M for LXM28... at 2.6 A, 220 V, three phase 2.86 N.m for LXM28... at 5.7 A, 110 V, single phase
Nominal speed	1000 rpm for LXM26D at 2.6 A, 220 V, single phase 1000 rpm for LXM26D at 2.6 A, 220 V, three phase 1000 rpm for LXM28... at 2.6 A, 220 V, single phase 1000 rpm for LXM28... at 2.6 A, 220 V, three phase 1000 rpm for LXM28... at 5.7 A, 110 V, single phase
Maximum current Irms	5.98 A for LXM28... at 0.3 kW, 220 V 5.98 A for LXM28... at 0.3 kW, 110 V
Maximum permanent current	2.09 A
Product compatibility	LXM26D servo drive motor at 0.3 kW, 220 V, single phase LXM26D servo drive motor at 0.3 kW, 220 V, three phase LXM28... servo drive motor at 0.3 kW, 220 V, single phase LXM28... servo drive motor at 0.3 kW, 220 V, three phase LXM28... servo drive motor at 0.3 kW, 110 V, single phase
Shaft end	Keyed
Shaft diameter	22 mm
Shaft length	45 mm

Key width	8 mm
Feedback type	20 bits single turn absolute encoder
Holding brake	With
Holding torque	9.6 N.m built-in
Mounting support	Asian standard flange
Motor flange size	130 mm
Electrical connection	Connector MIL
Torque constant	1.52 N.m/A at 20 °C
Back emf constant	92 V/krpm at 20 °C
Rotor inertia	6.91 kg.cm ²
Stator resistance	1.93 Ohm at 20 °C
Stator inductance	24.9 mH at 20 °C
Stator electrical time constant	12.9 ms at 20 °C
Maximum radial force Fr	670 N at 1000 rpm
Maximum axial force Fa	200 N
Brake pull-in power	19.7 W
Type of cooling	Natural convection
Length	183 mm
Number of motor stacks	1
Centring collar diameter	110 mm
Centring collar depth	8 mm
Number of mounting holes	4
Mounting holes diameter	9.2 mm
Circle diameter of the mounting holes	145 mm
Distance shaft shoulder-flange	8 mm
Net weight	8.2 kg

Environment

IP degree of protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient air temperature for operation	0...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.000 cm
Package 1 Width	24.000 cm
Package 1 Length	36.200 cm
Package 1 Weight	8.945 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1679