




Datasheet

Product Name:	MIL-W-22759/9 28AWG
Product Discription:	MIL-W-22759/9 28AWG
Specification No.:	
Customer's Name:	

Description					Construction				
Rated Voltage:	1000V				Conductor	Stranded Sliver plated copper			
Rated Temperature:	200°C				Size(AWG)	28			
Reference Standard:	MIL-W-22759/9				Construction(±0.008mm)	7/0.127			
Cross Section					Stranded Dia.(mm)Ref.	0.38			
					Insulation Material	PTFE			
					Insulation Color	ANY COLOR			
					Ave Thickness(mm)	0.38			
					Insulation Dia.(±0.08mm)	1.14			
Marking					Remark:				
No marking on the cable jacket					8776137 Red 8776128 Blue 8776121 Black 8776130 White 8776124 Brown				
Applications					Characteristics				Customer Approve
These wires are ideal for internal wiring of appliances, electronic equipment and other applications.					Test Item	Standard Value			Seal & Stamp Signature: Date:
					Test Material	PTFE(ROHS)			
					Insulation resistance(20°C MΩ*m)	1000			
					Vol. Tesr(AC.V.60S) (V)	2000			
					Flammability Test	VW-1			
					Max.DC Resistance(20°C Ω/km)	208.66(MAX)			
Revisions									
Version	Description	Drawn by	Approved by	Date					
0	New document issue	Danniel	Jason	19/05/2015					