SIEMENS

# Data sheet for SINAMICS G120X

## Article No. : 6SL3230-3YE28-0AB0




Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

### Rated data

**Input**

| | | |
|---|---|---|
| Number of phases | 3 AC | |
| Line voltage | 380 ... 480 V +10 % -20 % | |
| Line frequency | 47 ... 63 Hz | |
| **Rated voltage** | **400V IEC** | **480V NEC** |
| Rated current (LO) | 29.50 A | 26.00 A |
| Rated current (HO) | 24.50 A | 21.30 A |

**Output**

| | | |
|---|---|---|
| Number of phases | 3 AC | |
| **Rated voltage** | **400V IEC** | **480V NEC** [1] |
| Rated power (LO) | 15.00 kW | 20.00 hp |
| Rated power (HO) | 11.00 kW | 15.00 hp |
| Rated current (LO) | 32.00 A | 27.00 A |
| Rated current (HO) | 26.00 A | 21.00 A |
| Rated current (IN) | 33.00 A | |
| Max. output current | 43.00 A | |
| Pulse frequency | 4 kHz | |
| Output frequency for vector control | 0 ... 200 Hz | |
| Output frequency for V/f control | 0 ... 550 Hz | |

**Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

### General tech. specifications

| | |
|---|---|
| Power factor λ | 0.70 ... 0.85 |
| Offset factor cos φ | 0.96 |
| Efficiency η | 0.98 |
| Sound pressure level (1m) | 67 dB |
| Power loss [3] | 0.438 kW |
| Filter class (integrated) | RFI suppression filter for Category C2 |
| EMC category (with accessories) | Category C2 |
| Safety function "Safe Torque Off" | without SIRIUS device (e.g. via S7-1500F) |

### Communication

| | |
|---|---|
| Communication | USS, Modbus RTU, BACnet MS/TP |

### Inputs / outputs

**Standard digital inputs**

| | |
|---|---|
| Number | 6 |
| Switching level: 0 → 1 | 11 V |
| Switching level: 1 → 0 | 5 V |
| Max. inrush current | 15 mA |

**Fail-safe digital inputs**

| | |
|---|---|
| Number | 1 |

**Digital outputs**

| | |
|---|---|
| Number as relay changeover contact | 2 |
| Output (resistive load) | DC 30 V, 5.0 A |
| Number as transistor | 0 |

**Analog / digital inputs**

| | |
|---|---|
| Number | 2 (Differential input) |
| Resolution | 10 bit |

**Switching threshold as digital input**

| | |
|---|---|
| 0 → 1 | 4 V |
| 1 → 0 | 1.6 V |

**Analog outputs**

| | |
|---|---|
| Number | 1 (Non-isolated output) |

**PTC/ KTY interface**

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C

### Closed-loop control techniques

| | |
|---|---|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC) | Yes |
| V/f ECO linear / square-law | Yes |
| Sensorless vector control | Yes |
| Vector control, with sensor | No |
| Encoderless torque control | No |
| Torque control, with encoder | No |

SIEMENS

## Data sheet for SINAMICS G120X

**Article No. :** **6SL3230-3YE28-0AB0**

### Ambient conditions

| | |
|---|---|
| Standard board coating type | Class 3C3, according to IEC 60721-3-3: 2002 |
| Cooling | Air cooling using an integrated fan |
| Cooling air requirement | 0.018 m³/s (0.653 ft³/s) |
| Installation altitude | 1,000 m (3,280.84 ft) |
| **Ambient temperature** | |
| Operation | -20 ... 45 °C (-4 ... 113 °F) |
| Transport | -40 ... 70 °C (-40 ... 158 °F) |
| Storage | -25 ... 55 °C (-13 ... 131 °F) |
| **Relative humidity** | |
| Max. operation | 95 % At 40 °C (104 °F), condensation and icing not permissible |

### Connections

| | |
|---|---|
| **Signal cable** | |
| Conductor cross-section | 0.15 ... 1.50 mm² (AWG 24 ... AWG 16) |
| **Line side** | |
| Version | screw-type terminal |
| Conductor cross-section | 1.50 ... 16.00 mm² (AWG 16 ... AWG 6) |
| **Motor end** | |
| Version | Screw-type terminals |
| Conductor cross-section | 1.50 ... 16.00 mm² (AWG 16 ... AWG 6) |
| **DC link (for braking resistor)** | |
| PE connection | On housing with M4 screw |
| **Max. motor cable length** | |
| Shielded | 150 m (492.13 ft) |

### Mechanical data


| | |
|---|---|
| Degree of protection | IP20 / UL open type |
| Frame size | FSC |
| Net weight | 7.66 kg (16.89 lb) |
| **Dimensions** | |
| Width | 140 mm (5.51 in) |
| Height | 295 mm (11.61 in) |
| Depth | 218 mm (8.58 in) |

### Standards

| | |
|---|---|
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH |
| CE marking | EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC |

### Converter losses to IEC61800-9-2*

| | |
|---|---|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 39.1 % |




The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

[1] The output current and HP ratings are valid for the voltage range 440V-480V

[3] Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

## Data sheet for SINAMICS G120X

**Article No. :** **6SL3230-3YE28-0AB0**

### Operator panel: Intelligent Operator Panel (IOP-2)

#### Screen

| | |
|---|---|
| Display design | LCD color |
| Screen resolution | 320 x 240 Pixel |

#### Mechanical data

| | |
|---|---|
| Degree of protection | IP55 / UL type 12 |
| Net weight | 0.134 kg (0.30 lb) |
| **Dimensions** | |
| Width | 70.00 mm (2.76 in) |
| Height | 106.85 mm (4.21 in) |
| Depth | 19.65 mm (0.77 in) |

#### Ambient conditions

| | |
|---|---|
| **Ambient temperature** | |
| Operation | 0 ... 50 °C (32 ... 122 °F)<br>55 °C only with door installation kit |
| Storage | -40 ... 70 °C (-40 ... 158 °F) |
| Transport | -40 ... 70 °C (-40 ... 158 °F) |
| **Relative humidity at 25°C during** | |
| Max. operation | 95 % |

#### Approvals

| | |
|---|---|
| Certificate of suitability | CE, cULus, EAC, KCC, RCM |