

KSB160DD411

Tap off unit, Canalis KS 100A to 1000A, for
ComPacT NSX100/160, with plug in base,
160A, 3L+N+PE, IP55, RAL9001



Main

Range of product	Canalis
Range compatibility	Canalis KS busbar trunking
Offer type	Advanced
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KS busbar trunkingplug-in
[Ie] rated operational current	160 A at 35 °C
Protection type	Circuit breaker: Compact NSX100 Circuit breaker: Compact NSX160
Provided equipment	Circuit-breaker to be ordered separately
Mounting mode	Plug-in with fixed polarity
Tap-off unit polarity	3L+N+PE
Colour	White (RAL 9001)


Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	400 V depending on protective device 500 V depending on protective device
[Uimp] rated impulse withstand voltage	6.8 kV
[Ui] rated insulation voltage	400 V depending on protective device 500 V depending on protective device
Network frequency	50/60 Hz
Control type	Extended rotary handle
Electrical connection	Crimp lug - ISO32 70 mm ² flexible Crimp lug - ISO32 70 mm ² rigid
Door/cover opening side	Right
Tap-off unit disconnection mode	By opening the door
Number of openings	1 opening for FL21 gland plate
Standards	IEC 61439-6 IEC 61439-1
Body material	Metal
Width	450 mm
Depth	310 mm
Depth (door open)	727 mm
Net weight	15 kg

Environment

Earthing system	TT TN-S IT
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins