

# ph/temperature measuring instrument

testo 206

---

Ideally suited to applications in liquid and semi-solid media  
(e.g. in the food sector)

---

Built-in temperature sensor

---

Maintenance-free gel electrolyte

---

Robust, waterproof and dishwasher-safe protective cover  
(TopSafe, protection class IP65)

---

Automatic final value recognition (Auto-hold)

---

Two-line display

---

1, 2, or 3-point calibration possible

---



pH

°C

The testo 206 series is ideally suited for applications in liquid and semi-solid media. The instruments stand out thanks to the combination of a pH immersion probe and a temperature probe for precise and fast temperature compensation. Thanks to the large volume of gel electrolyte and the dual wall diaphragm, the probe is leak-proof, maintenance-free and insensitive to dirt. The automatic final value recognition supports the user during measurement. The protective cover TopSafe provides the instruments with the protection class IP65, it is dishwasher-safe, hygienic and protects the measuring instrument from dirt, water and impact.

The testo 206-pH1 is specially designed for fast pH checks in liquids.

The testo 206-pH2 is ideally suited for pH measurement in semi-solid and protein-rich foods such as jellies, creams, cheese, fruit etc.

The testo 206-pH3 is equipped with a BNC socket which allows the connection of any pH probes to the instrument, depending on the application. This makes the instrument universally applicable.

## Technical data / Accessories

### testo 206 pH1

One-hand pH/°C measuring instrument, pH1 probe head for liquids, storage cap with gel, TopSafe and belt/wall holder

Part no. 0563 2061



#### Sensor type pH electrode

Meas. range	0 to 14 pH
Accuracy ±1 digit	±0.02 pH
Resolution	0.01 pH

#### Sensor type NTC

Meas. range	0 to 60 °C (Short-term to +80 °C max. 5 min)
Accuracy ±1 digit	±0.4 °C
Resolution	0.1 °C

### testo 206-pH1 Starter Set

One-hand pH/°C measuring instrument, pH1 probe head for liquids, storage cap with gel, calibration dosing bottles 250 ml pH 4+7, TopSafe, belt/wall holder and aluminium case

Part no. 0563 2065

#### General technical data

Oper. temp.	0 to +60 °C
Storage temp.	-20 to +70 °C
No. meas. channels	2 channel
Temperature compensation	Automatic
Meas. rate	2 measurements per second
Battery type	1x CR2032
Material/Housing	ABS with TopSafe, Protection type IP 68
Battery life	80 h (Auto Off 10 min)
Dimensions	197 x 33 x 20 mm
Weight	69 g
Display	LCD, 2 lines



Easy exchange of probes with testo 206-pH1/-pH2/-pH3



testo 206-pH1:  
pH1 probe head for liquids

#### Accessories

#### Part no.

##### Accessories for measuring instrument

Spare pH probe for testo 206 incl. gel storage cap	0650 2061	
Storage cap for testo 206 with KCl gel filling	0554 2067	
Lithium battery button cell	0515 0028	
pH buffer solution 4.01 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2061	
pH buffer solution 7.00 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2063	
pH buffer solution 10.01 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2065	

## Technical data / Accessories

### testo 206-pH2

One-hand pH/°C measuring instrument, pH2 probe head for semi-solid substances, storage cap with gel, TopSafe and belt/wall holder

Part no. 0563 2062




### General technical data

Oper. temp.	0 to +60 °C
Storage temp.	-20 to +70 °C
No. meas. channels	2 channel
Temperature compensation	Automatic
Meas. rate	2 measurements per second
Battery type	1x CR2032
Material/Housing	ABS with TopSafe, Protection type IP 68
Battery life	80 h (Auto Off 10 min)
Dimensions	197 x 33 x 20 mm
Weight	62 g
Display	LCD, 2 lines

### testo 206-pH2 Starter Set

One-hand pH/°C measuring instrument, pH2 probe head for semi-solid substances, storage cap with gel, calibration dosing bottles 250 ml pH 4+7, TopSafe, belt/wall holder and aluminium case

Part no. 0563 2066



testo 206-pH2:  
pH2 probe head for semi-solid food

### Sensor types

	pH electrode	NTC
Meas. range	0 to 14 pH	0 to 60 °C (Short-term to +80 °C max. 5 min)
Accuracy ±1 digit	±0.02 pH	±0.4 °C
Resolution	0.01 pH	0.1 °C

### Accessories

### Part no.


#### Accessories for measuring instrument

	Part no.
Spare pH probe pH2 for testo 206 incl. gel storage cap	0650 2062
Storage cap for testo 206 with KCl gel filling	0554 2067
Lithium battery button cell	0515 0028
pH buffer solution 4.01 in dosing bottle (250 ml) with DAkKS calibration certificate	0554 2061
pH buffer solution 7.00 in dosing bottle (250 ml) with DAkKS calibration certificate	0554 2063
pH buffer solution 10.01 in dosing bottle (250 ml) with DAkKS calibration certificate	0554 2065

## Technical data / Accessories

**testo 206-pH3**

One-hand pH/°C measuring instrument, pH3 probe head with BNC interface, TopSafe and belt/wall holder



Part no. 0563 2063

**testo 206-pH3 Versatile Set**

testo 206-pH3 set, one-hand pH/°C measuring instrument, pH3 probe head with BNC interface, pH universal plastic electrode with temperature sensor, incl. storage cap with gel, calibration dosing bottles 250 ml pH 4+7, TopSafe, belt/wall holder and aluminium case

Part no. 0563 2068

Sensor type	pH electrode / NTC
Meas. range	0 to 14 pH 0 to 80 °C (depending on the pH probe used)
Interface	BNC

**General technical data**

Oper. temp.	0 to +60 °C
Storage temp.	-20 to +70 °C
Battery life	80 h (Auto Off 10 min)
Dimensions	197 x 33 x 20 mm
Weight	69 g
Display	LCD, 2 lines



testo 206-pH3:  
pH3 probe head with BNC interface

Accessories	Part no.
<b>Accessories for measuring instrument</b>	
pH universal plastic electrode without temperature sensor	0650 2063
pH universal plastic electrode with temperature sensor	0650 2064
Glass pH electrode with temperature sensor	0650 1623
pH food electrode without temperature sensor	0650 0245
Lithium battery button cell	0515 0028
Storage solution; 50ml, for electrode 0650 0245	0554 2318
Gel storage cap for standard electrodes	0554 2053
pH buffer solution 4.01 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2061
pH buffer solution 7.00 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2063
pH buffer solution 10.01 in dosing bottle (250 ml) with DAkkS calibration certificate	0554 2065

