


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical wear
- **Plain Conductor Type:** Ensures consistent performance and ease of installation
- **24/0.2 Core Strands:** Enhances flexibility for easy routing in tight spaces
- **Wide Temperature Range (-15 °C to 90 °C):** Suitable for various environmental conditions
- **500 V Voltage Rating:** Supports high-voltage applications

RS PRO 0.75 mm² Flexible Cable, 100 m

RS Stock No: 606-111



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for applications requiring flexibility and resilience, making it ideal for installations where space is limited.

General Specifications

| | |
|--------------------|-----------------|
| Conductor Material | Annealed Copper |
| Conductor Type | Plain |
| Jacket Colour | White |
| Product Type | Flexible Cable |

Mechanical Specifications

| | |
|------------------|----------------------|
| Cable CSA | 0.75 mm ² |
| Cable Length | 100 m |
| Core Strands | 24/0.2 |
| Jacket Material | Polyvinyl Chloride |
| Number of Cores | 3 |
| Outside Diameter | 7.6 mm |

Operation Environment Specifications

| | |
|-------------------------------|--------|
| Maximum Operating Temperature | 90 °C |
| Minimum Operating Temperature | -15 °C |

Approvals

| | |
|---------------------|---|
| Standards/Approvals | ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228 |
|---------------------|---|

Electrical Specifications

| | |
|---------|-------|
| Voltage | 500 V |
|---------|-------|