

ToLEDo Retro Candle Dimmable

ToLEDo RT DIM CAND GL 260LM 1700K E14 SL

0027113



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Golden
Lamp shape	Candle
Colour temperature (K)	1700
CRI (Ra)	80
Dimmable	Yes
EAN code	5410288271132
Energy class	A+
Equivalent watt (W)	26
Cap/Base	E14
Type	ToLEDo Retro Candle Dimmable
Watt (Nominal) (W)	4.5
Light colour	MagmaGlow
Ordering number	0027113
Efficacy (Rated) (lm/w)	57.77
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	260
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

Average life (Nominal) (h)	15000
Control gear required	No
Lamp finish	Golden
Lamp shape	Candle
Dimmable	Yes
Dry applications use only	Yes
EAN code	5410288271132
Energy class	A+

ToLEDo Retro Candle Dimmable

ToLEDo RT DIM CAND GL 260LM 1700K E14 SL

0027113

Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	E14
Lamp mercury content (mg)	0
Type	ToLEDo Retro Candle Dimmable
No. of switching cycles before premature failure (min)	>50,000
Optimal operating condition (°C)	25
Ordering number	0027113
Product name	ToLEDo RT DIM CAND GL 260LM 1700K E14 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Colour temperature (K)	1700
CRI (Ra)	80
Light colour	MagmaGlow
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	260
Luminous flux (Rated) (lm)	260
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Drive current (mA)	27
Equivalent watt (W)	26
kWh per 1000 hours burning time	5
Lamp power factor	0.8
Watt (Nominal) (W)	4.5
Efficacy (Rated) (lm/w)	57.77
Watt (Rated) (W)	4.5
Voltage (V)	220-240

Physical data

Max. Lamp Diameter (mm) - D	35
------------------------------------	----

ToLEDo Retro Candle Dimmable

ToLEDo RT DIM CAND GL 260LM 1700K E14 SL

0027113

Lamp Length (mm) - C/L	117
Lamp dimension equal to filament lamp equivalent	Yes

TECHNICAL DRAWINGS

