

10EJT1F

✓ ACTIVE

Corcom | Corcom EJT


TE Internal #: 4-1609157-3

Power Line, Vertical, 10 A, .250" FASTON Output, 250 VAC,
Filtered, IEC 60320-1 C-14, Corcom EJT, Power Entry Modules

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Entry Modules > IEC Filtered Inlets, Corcom EJT Series



Filter Type: **Power Line**
Product Orientation: **Vertical**
Leakage Current (Max) (120VAC, 60Hz): **250 μ A**
Current Rating: **10 A**
Output Termination Type: **.250" FASTON**

[All IEC Filtered Inlets, Corcom EJT Series \(22\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Vertical
---------------------	----------

Mechanical Attachment

Panel Mount Feature Type	Extended Flange
--------------------------	-----------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom EJT



Power Entry Modules(22)

Customers Also Bought



TE Part #350761-4
04P UMNL HDR ASSY PC




TE Part #350762-4
06P UMNL HDR ASSY PC




TE Part #316454-1
M-U-M-N-L PLUG CABLE CLAMP




TE Part #640389-4
04P MTA156 HDR ASSY SQ R/A F/L



TE Part #640389-2
02P MTA156 HDR ASSY SQ R/A F/L



TE Part #350763-4
09P UMNL HDR ASSY PC



TE Part #350764-4
12P UMNL HDR ASSY PC



TE Part #640467-1
05P UMNL HDR ASSY



TE Part #350765-4
15P UMNL HDR ASSY PC



TE Part #350760-4
03P UMNL HDR ASSY PC

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1609157-3_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1609157-3_B.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_4-1609157-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Corcom EJT Flanged Inlet Filter](#)

English

[Corcom Combined Selector Charts](#)

English