

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· **1.1 Product identifier**

· Trade name: **Zep® Contractors Solvent & Degreaser**

· Article number: 47140007

· UFI: S16E-8UD8-3C4J-97PK

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**

· **Sector of Use**

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

· **Product category PC35** Washing and cleaning products (including solvent based products)

· **Technical function** Cleaning agent

· **Application of the substance / the mixture** Cleaner solvent

· **1.3 Details of the supplier of the safety data sheet**

· **Manufacturer/Supplier:**

ZEP UK Ltd

Tanhouse Lane

Widnes Cheshire, WA8 0RD

United Kingdom

Tel: +44 (0)151 422 1000

Fax: +44 (0)151 422 1011

@: info@zep.co.uk

web: www.zep.co.uk

ZEP Industries BV

Vierlinghweg 30

4612 PN Bergen op Zoom

The Netherlands

Tel: (NL) + 31 164 250 100 (B) + 32 2 347 0117

Fax: (NL) + 31 164 266 710 (B) + 32 2 347 1395

@: sales@zepbenelux.com

ZEP ITALIA SRL

Via Netunese Km. 25.000

04011 Aprilia (LT) - Italy

Tel: +39.06.926691

Fax: +39.06.92747061

@: tecnico@zepeurope.com

Sito: www.zep.it

· **Further information obtainable from:**

Customer Service

NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710

B: Tel: +32 2 347 0117 Fax: +32 2 347 1395

IT: Tel: +39 069 266 91 Fax: +39 06.927 470 61

UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011

· **1.4 Emergency telephone number:**

Customer Service

NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710

B: Tel: +32 2 347 0117 Fax: +32 2 347 1395

IT: Tel: +39 069 266 91 Fax: +39 06.927 470 61

UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011

EU: Tel. 112

SECTION 2: Hazards identification

· **2.1 Classification of the substance or mixture**

· **Classification according to Regulation (EC) No 1272/2008**

Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.

· **2.2 Label elements**

· **Labelling according to Regulation (EC) No 1272/2008** The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 1)

· Hazard pictograms



GHS08

· Signal word *Danger*

· Hazard-determining components of labelling:

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

· Hazard statements

H304 May be fatal if swallowed and enters airways.

· Precautionary statements

P102 Keep out of reach of children.

P301+P310 IF SWALLOWED: Immediately call a doctor.

P301+P330+P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.

P302+P352 IF ON SKIN: Wash with plenty of water/and soap

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

· Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking.

· 2.3 Other hazards The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds.

· Results of PBT and vPvB assessment

· PBT: Not applicable.

· vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

· Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:

EC number: 926-141-6	Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics	75-100%
Reg.nr.: 01-2119456620-43	Asp. Tox. 1, H304	

· Ingredients according to Detergents Regulation 648/2004/EC

For the wording of the listed hazard phrases refer to section 16.

Aliphatic hydrocarbons	≥30%
------------------------	------

SECTION 4: First aid measures

· 4.1 Description of first aid measures

· General information: Immediately remove any clothing soiled by the product.

· After inhalation: Supply fresh air; consult doctor in case of complaints.

· After skin contact:

If skin irritation continues, consult a doctor.

Immediately wash with water and soap and rinse thoroughly.

· After eye contact: Rinse opened eye for several minutes under running water. Then consult a doctor.

· After swallowing: Do not induce vomiting; call for medical help immediately.

· 4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.

· 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

SECTION 5: Firefighting measures

· 5.1 Extinguishing media

· Suitable extinguishing agents: CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

· 5.2 Special hazards arising from the substance or mixture No further relevant information available.

· 5.3 Advice for firefighters

· Protective equipment: No special measures required.

GB

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 2)

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, universal binders).
Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Use only in well ventilated areas.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Provide solvent resistant, sealed floor.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

8.1 Control parameters

- **Ingredients with limit values that require monitoring at the workplace:**

34590-94-8 Dipropylene glycol monomethyl ether (2.5-5%)

WEL (Great Britain)	Long-term value: 308 mg/m ³ , 50 ppm Sk
IOELV (European Union)	Long-term value: 308 mg/m ³ , 50 ppm Skin

- **Additional information:** The lists valid during the making were used as basis.

8.2 Exposure controls

- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
- **Respiratory protection:**
Filter AX
Not necessary if room is well-ventilated.
- **Protection of hands:**



Protective gloves

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed. The determined penetration times according to EN 374 part III are not performed under practical conditions. Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended.

- **For the permanent contact gloves made of the following materials are suitable:**

Nitrile rubber, NBR

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 3)

PVA gloves

- **Not suitable are gloves made of the following materials:** Strong material gloves
- **Eye protection:** Goggles recommended during refilling
- **Body protection:** Solvent resistant protective clothing

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

· Form:	Liquid
· Colour:	Colourless
· Odour:	Solvent-like
· Odour threshold:	Not determined.

· Change in condition

· Melting point/freezing point:	Undetermined.
· Initial boiling point and boiling range:	189 °C

· **Flash point:** 67 °C

· **Flammability (solid, gas):** Not applicable.

· **Ignition temperature:** 230 °C

· **Decomposition temperature:** Not determined.

· **Auto-ignition temperature:** Product is not selfigniting.

· **Explosive properties:** Product does not present an explosion hazard.
Not determined.

· Explosion limits:

· Lower:	0.6 Vol %
· Upper:	6 Vol %

· **Vapour pressure at 20 °C:** 0.1 hPa

· **Density at 20 °C:** 0.8 g/cm³

· **Relative density** Not determined.

· **Vapour density** Not determined.

· **Evaporation rate** Not determined.

· Solubility in / Miscibility with water:

Insoluble.

· **Partition coefficient: n-octanol/water:** Not determined.

· Viscosity:

· Dynamic:	Not determined.
· Kinematic:	Not determined.

· Solvent content:

· Organic solvents:	100.0 %
· Swiss VOC:	3.00 %

· **Solids content:** 0.0 %

· **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

· **10.1 Reactivity** No further relevant information available.

· **10.2 Chemical stability**

· **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

· **10.3 Possibility of hazardous reactions** No dangerous reactions known.

· **10.4 Conditions to avoid** No further relevant information available.

· **10.5 Incompatible materials:** No further relevant information available.

· **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

GB

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 4)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

Oral	LD50	>5,000 mg/kg (Rat) (OECD 401)
Dermal	LD50	>5,000 mg/kg (Rabbit) (OECD 402 (24 h))
Inhalative	LC50/ 8 h	>5,000 mg/m ³ (Rat) (OECD 403)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard**
May be fatal if swallowed and enters airways.

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

Hydrocarbons, C11-C14, n-alkanes, isoalkanes, cyclics, <2% aromatics

EL50 (48 h)	>1,000 mg/l (<i>Daphnia magna</i> (water flea)) (OECD 202)
OECD test 301 F	69 % (biodegradation in % after 28 days) Readily Biodegradable

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:** Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Disposal must be made according to official regulations
Can be disposed of with household garbage after consulting with the waste disposal facility operator and the pertinent authorities and adhering to the necessary technical regulations.
- **Uncleaned packaging:**
- **Recommendation:** Disposal in accordance with administrative provisions

SECTION 14: Transport information

- | | |
|--|------|
| <ul style="list-style-type: none"> · 14.1 UN-Number · ADR, ADN, IMDG, IATA | Void |
| <ul style="list-style-type: none"> · 14.2 UN proper shipping name · ADR, ADN, IMDG, IATA | Void |

(Contd. on page 6)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 5)

· 14.3 Transport hazard class(es)	
· ADR, ADN, IMDG, IATA	
· Class	Void
· 14.4 Packing group	
· ADR, IMDG, IATA	Void
· 14.5 Environmental hazards:	Not applicable.
· 14.6 Special precautions for user	Not applicable.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· UN "Model Regulation":	Void

SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

Reg. (EC) n. 1272/2008 - CLP;
 Reg. (EC) n. 1907/2006 – Reach;
 Reg. (EC) n. 2015/830 annex II of REACH;
 Reg. (EC) n. 648/04 (Detergents);
 Reg. (EC) n. 528/12 (Biocides BPR);
 Reg. (EC) n. 1223/2009 (Cosmetics);
 Dir. 06/08 ADR – RID - IMDG - IATA;
 Dir. 47/08 (Aerosols); Dir. 12/18 (Seveso III);
 Dir. 2008/98/CE and Reg. (EC) n.1357/2014 (Waste management)

- Directive 2012/18/EU
- Named dangerous substances - ANNEX I None of the ingredients is listed.
- REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- National regulations:

· **Technical instructions (air):**

Class	Share in %
NK	75-100

- **Waterhazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H304 May be fatal if swallowed and enters airways.

· **Department issuing SDS:**

Customer Service
 NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710
 B: Tel: +32 2 347 0117 Fax: +32 2 347 1395
 IT: Tel: +39 069 266 91Fax: +39 06.927 470 61
 UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011

· **Contact:**

Customer Service
 NL: Tel: + 31 164 250 100 Fax: + 31 164 266 710
 B: Tel: +32 2 347 0117 Fax: +32 2 347 1395
 IT: Tel: +39 069 266 91Fax: +39 06.927 470 61
 UK: Tel: +44 151 422 1000 Fax: +44 151 422 1011

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 EINECS: European Inventory of Existing Commercial Chemical Substances

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 6)

ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Asp. Tox. 1: Aspiration hazard – Category 1

· *** Data compared to the previous version altered.**

GB

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.07.2019

Version: 2

Revision: 26.07.2019

Trade name: Zep® Contractors Solvent & Degreaser

(Contd. of page 7)

Annex: Exposure scenario

· **Short title of the exposure scenario**

For the finished product.

Zep Commercial® Tar & Bitumen Remover

· **Sector of Use**

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

· **Description of the activities / processes covered in the Exposure Scenario** See section 1 of the annex to the Safety Data Sheet.

· **Conditions of use**

· **Duration and frequency** 5 workdays/week.

· **Physical parameters**

· **Physical state** Fluid

· **Concentration of the substance in the mixture** The substance is main component.

· **Used amount per time or activity**

According to directions for use.

Smaller than 10 g per application.

· **Other operational conditions**

· **Other operational conditions affecting environmental exposure** No special measures required.

· **Other operational conditions affecting consumer exposure** Keep out of the reach of children.

· **Other operational conditions affecting consumer exposure during the use of the product** Not applicable.

· **Risk management measures**

· **Worker protection**

· **Organisational protective measures** No special measures required.

· **Technical protective measures**

Ensure that suitable extractors are available on processing machines

Use product only in enclosed systems.

· **Personal protective measures**

Do not inhale gases / fumes / aerosols.

Protective gloves

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Measures for consumer protection** Ensure adequate labelling.

· **Environmental protection measures**

· **Water** No special measures required.

· **Disposal measures** Ensure that waste is collected and contained.

· **Disposal procedures** Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **Waste type** Partially emptied and uncleaned packaging

GB