



Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 7-170994-1
JACK SCREW MALE



TE Part # 7-170994-2
JACK SCREW MALE

Customers Also Bought



TE Part #66108-5
III+ SKT,26-24,30AU>10,STRIP



TE Part #917251-3
DYNAMIC D-3400F HDR ASSY 20P H



TE Part #DRC12-24PBE
REC, 24P, BLK, E, FLANGE, B



TE Part #87258-2
02 MODI HDR SRRA .156CL



TE Part #CAT-D9934-A75F
DYNAMIC 3200 HDR ASSY



TE Part #2-178293-3
DYNAMIC D3100 HDR H 3P ASSY



TE Part #3-582118-9
TEST PROBE REC130 BI WHT GPBR



TE Part #60080-2
250 FASTON TAB TPBR

Document

Product Drawings
JACK SCREW MALE

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_170994-1_C.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_170994-1_C.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_170994-1_C.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP Jack Screw Selection Chart for Series "M", COAXICON and Miniature

English

Instruction Sheet (U.S.)

English

AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS

English