

WHEEL DG 150X40/50 NYLON BEARING FIXED FORK X20

Wheel series DG

Wheels with elastic grey rubber ring on a thermoplastic core, with standard or stainless steel roller bearings or nylon friction bearings. The wheel is fitted with bushes.





Castor series INOX20

Inox20 series, polished stainless steel forks, swivels with double ball races.

Technical data

| | | |
|----------------------------|-----|------------|
| Wheel diameter | D | 150 mm |
| Tyre width | E | 40,0 mm |
| Bore diameter | d | 15 mm |
| Weight article | | 1,380 kg |
| Hub width | L | 50 mm |
| Overall height | H | 181 mm |
| Top plate outer dimensions | AxB | 135x110 mm |
| Bolt hole spacing | axb | 96x56 mm |
| Bolt hole spacing | axb | 105x75 mm |
| Bolt hole spacing | axb | 105x80 mm |
| Fixing bolt diameter | g | M10 |
| Fork width | U | 50 mm |
| Load Capacity | | 150 kg |



Related Articles

Spare part wheel: [13122G](#)

GENERAL INFORMATION / RECOMMENDATIONS AND WARNINGS

The cited text and the complete catalogue in their most up-dated versions are available in the OEM's website page www.lagspa.it/downloads. The dimensions, descriptions, specifications and illustrations herein are indicative and subject to variations without notice. The fact that products are illustrated herein does not necessarily imply they are available from stock nor does it place us under any obligation to supply them. Tests carried out refer to the original products with original accessories: the replacement of one of the components with others of different manufacture might prevent the same results from being achieved and will automatically invalidate any guarantee. Please contact our technical service concerning any special application.