



Datasheet

ENGLISH

Stock no. 133-6292

RS PRO 200 W LED High Bay - 24,000 lm



This quality LED high bay is designed to be used in industrial areas, warehouses and retail areas. Ideal for both new projects or retrofit solutions. Hi-Star LED lighting can provide superior illumination with excellent energy savings and provides years of maintenance free service. There is no warm up time with the Hi-Star LED units and the lifespan is not affected by switching on and off. The aluminium heatsink housing is designed to dissipate heat and doesn't contain any other cooling devices. Typical energy savings would be in excess of 85% compared to metal halide with an average payback period of less than 1 year.

Key Features

- Instant Light - No warm up
- Sleek compact design
- Tempered clear glass protector & steel bracket
- 150W: 18000 lumens or 200W: 24000 lumens
- Ultra low power consumption
- Designed to meet IP65
- 50,000 hour rated life
- Ideal for warehouse, workshops & car parks
- Mean Well LED driver
- Bridelux LED chip
- 6000K cool white colour temperature
- 120° even light distribution
- AC 85-265V, 50/60HZ
- Robust aluminium casing
- Maintenance free
- Useful life at 70% of performance: 28000H - 30000H
- Harmonic Distortion: <20%