


- Slot Drill
- Langlochfräser
- Spiebaanfrezen
- Fraises à rainurer
- Fresas Frontales
- Fresa de Ranhurar



C110



- 1.1 1.2 4.1 5.1 6.1 6.2 6.3
- 1.3 1.4 2.1 3.1 3.2 3.3 3.4 4.2 5.2 7.1 7.2 7.3 8.1

d_1 Ø mm	d_2 Ø mm	l_2 mm	l_1 mm	z	e-Code	d_1 Ø mm	d_2 Ø mm	l_2 mm	l_1 mm	z	e-Code
1.00	6	2.5	47	2	C1101.0	11.70	12	13	70	2	C11011.7
1.50	6	3	47	2	C1101.5	12.00	12	16	73	2	C11012.0
1.80	6	3	47	2	C1101.8	12.50	12	16	73	2	C11012.5
2.00	6	4	48	2	C1102.0	12.70	12	16	73	2	C11012.7
2.50	6	5	49	2	C1102.5	13.00	12	16	73	2	C11013.0
2.80	6	5	49	2	C1102.8	13.70	12	16	73	2	C11013.7
3.00	6	5	49	2	C1103.0	14.00	12	16	73	2	C11014.0
3.50	6	6	50	2	C1103.5	15.00	12	16	73	2	C11015.0
3.80	6	7	51	2	C1103.8	15.70	16	19	79	2	C11015.7
4.00	6	7	51	2	C1104.0	16.00	16	19	79	2	C11016.0
4.50	6	7	51	2	C1104.5	17.00	16	19	79	2	C11017.0
4.80	6	8	52	2	C1104.8	17.70	16	19	79	2	C11017.7
5.00	6	8	52	2	C1105.0	18.00	16	19	79	2	C11018.0
5.50	6	8	52	2	C1105.5	19.00	16	19	79	2	C11019.0
5.75	6	8	52	2	C1105.75	19.70	20	22	88	2	C11019.7
6.00	6	8	52	2	C1106.0	20.00	20	22	88	2	C11020.0
6.50	10	10	60	2	C1106.5	21.70	20	22	88	2	C11021.7
6.75	10	10	60	2	C1106.75	22.00	20	22	88	2	C11022.0
7.00	10	10	60	2	C1107.0	24.00	25	26	102	2	C11024.0
7.50	10	10	60	2	C1107.5	24.70	25	26	102	2	C11024.7
7.75	10	11	61	2	C1107.75	25.00	25	26	102	2	C11025.0
8.00	10	11	61	2	C1108.0	26.00	25	26	102	2	C11026.0
8.50	10	11	61	2	C1108.5	28.00	25	26	102	2	C11028.0
9.00	10	11	61	2	C1109.0	30.00	25	26	102	2	C11030.0
9.50	10	11	61	2	C1109.5	32.00	32	32	112	2	C11032.0
9.70	10	13	63	2	C1109.7	36.00	32	32	112	2	C11036.0 ¹⁾
10.00	10	13	63	2	C11010.0	40.00	40	38	130	2	C11040.0 ¹⁾
10.50	12	13	70	2	C11010.5	45.00	40	38	130	2	C11045.0 ¹⁾
11.00	12	13	70	2	C11011.0	50.00	50	45	147	2	C11050.0 ¹⁾
11.50	12	13	70	2	C11011.5						

¹⁾ HSCo