



Brand of **NTN corporation**

## Technical data


**24038EAW33C3**

Spherical roller bearings



**ULTAGE**

### VISUAL (S)



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15



PRODUCT DEFINITION

|                                |          |
|--------------------------------|----------|
| Brand                          | SNR      |
| d - Internal diameter          | 190 mm   |
| D - External diameter          | 290 mm   |
| B - Bearing/Inner ring width   | 100 mm   |
| D1 - Inner diameter outer ring | 263,2 mm |
| rs - Min fillet radius         | 2,1 mm   |
| Number of lubrication holes    | 3        |
| b - Groove width               | 13 mm    |
| k - Hole diameter              | 6 mm     |
| Radial clearance class         | C3       |
| Mass                           | 23,42 kg |

PRODUCT PERFORMANCE

|                  |               |
|------------------|---------------|
| C - Dynamic load | 1360000000 mN |
|------------------|---------------|



## PRODUCT PERFORMANCE

|                                           |               |
|-------------------------------------------|---------------|
| <b>C0 - Static load</b>                   | 2000000000 mN |
| <b>Cu - Fatigue limit load</b>            | 187000000 mN  |
| <b>e - Coefficient</b>                    | 0.3           |
| <b>Y0 - Static axial load coefficient</b> | 2.18          |
| <b>Y1 - Lower axial load coefficient</b>  | 2.23          |
| <b>Y2 - Upper axial load coefficient</b>  | 3.32          |
| <b>N ref - Reference thermal speed</b>    | 7800 °/s      |
| <b>N lim - Mechanical Limit Speed</b>     | 12600 °/s     |
| <b>Tmin - Min operating temperature</b>   | 233,15 °K     |
| <b>Tmax - Max operating temperature</b>   | 473,15 °K     |

## BEARING FREQUENCIES

|                                                                 |           |
|-----------------------------------------------------------------|-----------|
| <b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>     | 11.135 Hz |
| <b>BPFI - Over rolling frequency on inner (60 rpm)</b>          | 13.865 Hz |
| <b>BSF - Over rolling frequency on rolling element (60 rpm)</b> | 8.866 Hz  |
| <b>BRF - Rotational frequency - rolling element (60 rpm)</b>    | 4.433 Hz  |
| <b>FTF - Rotational frequency - cage (60 rpm)</b>               | 0.445 Hz  |

## ABUTMENT

|                                                       |        |
|-------------------------------------------------------|--------|
| <b>da min - Min shoulder diameter IR</b>              | 202 mm |
| <b>Da max - Max shoulder diameter OR</b>              | 278 mm |
| <b>ra max - Max shaft &amp; housing fillet radius</b> | 2 mm   |



## INDUSTRY CALCUL FACTORS

### Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

| $F_a / F_r \leq e$ |    | $F_a / F_r > e$ |    |
|--------------------|----|-----------------|----|
| X                  | Y  | X               | Y  |
| 1                  | Y1 | 0.67            | Y2 |

### Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

| $X_0$ | $Y_0$ |
|-------|-------|
| 1     | Y0    |

The values for e, Y1, Y2 and Y0 are shown in the above table .

