

# C63R36M500

circuit breaker ComPacT NSX630R, 200 kA at 415 VAC, MicroLogic 6.3 E-M trip unit 500 A, 3 poles 3d



## Main

Range	ComPacT new generation
Product name	ComPacT NSX new generation
Device short name	NSX630R
Product or component type	Circuit breaker
Device application	Motor protection
Poles description	3P
Protected poles description	3D
[In] rated current	500 A at 65 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	200 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	R 200 kA 415 V AC
Trip unit name	Micrologic 6.3 E-M
Trip unit technology	Electronic
Trip unit protection functions	LSIG
Control type	Toggle
Circuit breaker mounting mode	Fixed

## Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ics] rated service short-circuit breaking capacity	200 KA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 KA at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	15000 cycles
Electrical durability	8000 Cycles at 440 V In/2 4000 Cycles at 440 V In 6000 Cycles at 690 V In/2 2000 cycles at 690 V In
Power dissipation per pole	25 W

Mounting support	Backplate
Mounting position	Horizontal and vertical Flat on the back
Upside connection	Front
Downside connection	Front
Connection pitch	45 mm
Protection type	L : for overload protection (long time) So : for short time short-circuit protection I : for instantaneous short-circuit protection G : for ground fault protection
Trip unit rating	500 A at 65 °C
Motor tripping class	5 30 20 10
Complementary motor protection	Stalled rotor Phase unbalance Protracted starting time Underload
Long-time pick-up adjustment type I <sub>r</sub> (thermal protection)	Adjustable 9 settings
[I <sub>r</sub> ] long-time protection pick-up adjustment range	250...500 A
Long-time protection delay adjustment type t <sub>r</sub>	Adjustable
[t <sub>r</sub> ] long-time protection delay adjustment range	120 S at 1.5 x I <sub>r</sub> for trip class 5 6.5 S at 6 x I <sub>r</sub> for trip class 5 5 S at 7.2 x I <sub>r</sub> for trip class 5 240 S at 1.5 x I <sub>r</sub> for trip class 10 13.5 S at 6 x I <sub>r</sub> for trip class 10 10 S at 7.2 x I <sub>r</sub> for trip class 10 480 S at 1.5 x I <sub>r</sub> for trip class 20 26 S at 6 x I <sub>r</sub> for trip class 20 20 S at 7.2 x I <sub>r</sub> for trip class 20 720 S at 1.5 x I <sub>r</sub> for trip class 30 38 S at 6 x I <sub>r</sub> for trip class 30 30 s at 7.2 x I <sub>r</sub> for trip class 30
Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type I <sub>sd</sub>	Adjustable
[I <sub>sd</sub> ] Short-time protection pick-up adjustment range	5...13 x I <sub>r</sub>
Short-time protection delay adjustment type t <sub>sd</sub>	Fixed
Instantaneous protection pick-up adjustment type I <sub>i</sub>	Fixed
[I <sub>i</sub> ] instantaneous protection pick-up adjustment range	6500 A
Ground-fault protection pick-up adjustment type I <sub>g</sub>	Adjustable 9 settings
[I <sub>g</sub> ] ground-fault protection pick-up adjustment range	0.2...1 x I <sub>n</sub> I <sub>g</sub> enable on/off
Ground-fault protection time delay adjustment type t <sub>g</sub>	Adjustable 5 settings
[t <sub>g</sub> ] ground-fault protection time delay adjustment range	0...0.4 s
Earth-leakage protection	Without
Zone selective interlocking ZSI	With
Number of slots for electrical auxiliaries	6 slot(s)
Local signalling	Flashing LED (green) for ready to operate LED 95 % I <sub>th</sub> (red) for temperature over set point
Display type	LCD display
Type of measurement	Energy meter
Communication of data	Demand current and power Time-stamped histories and event tables Maintenance indicators Maximeters/Minimeters Protection and alarm settings Instantaneous and demand values Energy metering Phase sequence Thermal image function Power quality
Width (W)	140 mm
Height (H)	255 mm

Depth (D)	110 mm
Net weight	6.2 kg

## Environment

Standards	EN/IEC 60947
Product certifications	EAC CCC Marine
Overvoltage category	Class II
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m without derating 2000 m...5000 m with derating

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	15.2 cm
Package 1 Length	29.2 cm
Package 1 Weight	5.81 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------