


ZMA80/120

Precision locknut

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information



Main Dimensions & Performance Data

d	M80X2	Thread
D	120 mm	Outside diameter
h	35 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	810,000 N	Breaking load, axial
M _L	285 Nm	Breakawag
M _{AL}	160 Nm	Mounting torque reference
M _M	44.6 kg*cm ²	Mass moment of inertia

≈m	1.723 kg	Weight
----	----------	--------

Dimensions

d ₁	105 mm	Plant diameter outside
t	4 mm	Hight retaining slot
b	8 mm	Width retaining slot
c	17.5 mm	Distance bore
m	M8	Threaded - threaded pin