

HRLSD-GTH 127K

Levelling castor, with integrated truck lock and top plate fitting, welded steel version, heavy duty wheel, with Blickle Extrathane® polyurethane tread, with cast iron wheel centre

EAN 4047526341299

ID 912086

Customs tariff number 87169090



Bracket: HRLSD series

- solid welded steel construction, zinc-plated, yellow-passivated, Cr6-free
- axial grooved ball bearing ISO 104 and tapered roller bearing ISO 355 in the swivel head
- dust and splash-proof
- welded guide sleeve for extremely strong truck lock
- wheels and truck lock can be levelled using a wrench (SW24)
- Grease nipple

Wheel: GTH series

- tread: high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A, colour yellow, non-marking, non-staining
- wheel centre: rugged grey cast iron, lacquered, colour silver

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +70 °C, temporarily up to +90 °C, reduced load capacity over +40 °C
- Floor clearance with screwed in truck lock and levelling screw

Technical data:

Wheel Ø (D)	☉ 125 mm
Wheel width	⊥ 50 mm
Number of wheels	2
Load capacity at 4 km/h	⚖ 1,300 kg
Bearing type	☉ ball bearing
Total height (H)	⊥ 170 mm
Max. total height (h)	⊥ 210 mm
Max foot floor clearance (T3)	40 mm
Mounting type	top plate
Plate size	📏 175 x 140 mm
Bolt hole spacing	📏 140 x 105 mm
Bolt hole Ø	🔧 14 mm
Offset (F)	☉ 70 mm
Temperature resistance min	-20 °C
Temperature resistance max	70 °C
Tread and tyre hardness	92 Shore A
Unit weight	⚖ 14.9 kg
Non-marking	✓
Non-staining	✓
Antistatic	✗
ESD	✗



Tread and tyre hardness

■ ■ ■ ■ ■ 92 Shore A

Rolling resistance



■ ■ ■ ■ ■ very good

Wear resistance

■ ■ ■ ■ ■ excellent

Operating noise / floor surface preservation

■ ■ ■ ■ ■ good



Electrically conductive		×
Corrosion-resistant		×
Heat-resistant		×
Tread hydrolysis-resistant		×
Suitable for autoclaves		×
Suitable for machine washing		×

Product references



Wheel used GTH 127/20-50K