


Shock absorber DYSD-Q11-5-5-Y1F-L-Y9

Part number: 8161520

FESTO



Data sheet

 General operating condition

Feature	Value
Size	5
Stroke	5 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Symbol	00991495
Max. impact speed	1 m/s
Reset time at room temperature	0.2 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Cushioning length	5 mm
Max. stop force	200 N
Max. energy consumption per stroke	2 J
Max. energy consumption per hour	8000 J
Max. residual energy	0.01 J
Reset force	7 N
Min. insertion force	27 N
Product weight	10 g
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel
Material nut	Galvanised steel