

## FANS

### HV-180E

#### Fan

Commercial grade high velocity fan



- 3 speed motor provides high velocity cooling
- Convenient carry handle
- Easy tilt air flow adjustment
- Heavy duty black nickel construction
- Reinforced steel grille keeps fingers away from blades
- Swivelling blade grille supplies good circulation of air
- Easy access front mounted control panel
- 4 position switch:
  - OFF
  - HI
  - MID
  - LOW



Technical information		HV-180E
Article-no.		6.518.001
EAN-no.		40 22167 518 019
Diameter blade	cm	45
Capacity	m <sup>3</sup> /h	5200
Power	Watt	135
Voltage/frequency	V~/Hz	230/50
Power settings		4
Colour		black
Dimensions retail package	LxWxH (cm)	59.0 x 22.0 x 56.0
Weight retail package	kg	8.9
Dimensions master carton	LxWxH (cm)	59.0 x 22.0 x 56.0
Weight master carton	kg	8.9
Number of packaging units	pieces	1

**Honeywell**

**Honeywell Hausgeräte GmbH**  
 Postfach 1246 · D-58732 Wickede  
 Telefon 0 23 77 / 92 89-0  
 Telefax 0 23 77 / 92 89-49