

Price\* : 150.46 GBP



## Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Range compatibility	Prisma P Prisma G
Type of ventilation filter	Standard
Air flow	Free flow rate with standard filter: 562 m <sup>3</sup> /h at 50 Hz Free flow rate with standard filter: 586 m <sup>3</sup> /h at 60 Hz
[Us] rated supply voltage	207...244 V
Input voltage	230 V 50/60 Hz

## Complementary

Power range	68 W 50 Hz 85 W 60 Hz
[In] rated current	0.52 A 50 Hz 0.37 A 60 Hz
Noise level	59 dB
Bearing type	Ball
Height	External: 336 mm
Width	External: 316 mm
Depth	External: 161 mm
Cut-out dimensions	291 x 291 mm
Product weight	3.2 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	-15...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	140 Pa flow rate 0 m <sup>3</sup> /h
Connections - terminals	Terminal block
IP degree of protection	IP54
Device composition	1 outlet grille front 1 axial motor

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

2 protective grille on the front and rear surfaces  
1 filter front of axial motor  
1 cut-out template

Condition of use

Outside temperature must be 5 °C lower than inside temperature  
Filter must be cleaned and replaced regularly  
Surrounding environment must be relatively clean  
Overfrequent filter replacement should be avoided  
Flow rates depends on the work point, see ProClima software

### Offer Sustainability

RoHS (date code: YYWW)

Compliant - since 0940 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH

Reference not containing SVHC above the threshold

[Reference not containing SVHC above the threshold](#)

### Contractual warranty

Warranty period

18 months 18 months