Product specifications

Eaton 109819

Catalog Number: 109819

Eaton Moeller® series DILMP Contactor, 4 pole, AC operation, AC-1: 45 A, 1 N/O, 110 V 50 Hz, 120 V 60 Hz, Screw terminals



General specifications

Product Name
Eaton Moeller® series DILMP 4-pole contactor

Catalog Number
109819

Model Code
DILMP45-10(110V50HZ,120V60HZ)

EAN
4015081093892

Product Length/Depth
97 mm

Product Height
85 mm

Product Width
58 mm

Product Weight
0.49 kg

Certifications
UL 60947-4-1
VDE 0660
CSA Class No.: 2411-03, 3211-04
UL File No.: E29096
CSA-C22.2 No. 60947-4-1-14
UL Category Control No.: NLDX
UL
IEC/EN 60947-4-1
CE
CSA File No.: 012528
IEC/EN 60947
CSA

Catalog Notes
Contacts according to EN 50012

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Number Of Poles

Four-pole

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Catalogs

Switching and protecting motors - catalog

Product Range Catalog Switching and protecting motors

SmartWire-DT Catalog

Characteristic curve

eaton-contactors-switching-dilmp-characteristic-curve.eps

eaton-contactors-characteristic-curve-2110dia-3.eps

Declarations of conformity

DA-DC-00004783.pdf

DA-DC-00004816.pdf

Drawings

eaton-contactors-dilmp-dimensions-008.eps

eaton-contactors-dilmp-dimensions-007.eps

eaton-contactors-mounting-dilm-dimensions.eps

eaton-contactors-mounting-dilm-dimensions-002.eps

eCAD model

DA-CE-ETN.DILMP45-10(110V50HZ,120V60HZ)

Installation instructions

IL03407049Z

Installation videos

WIN-WIN with push-in technology

mCAD model

DA-CD-dil_mp32_45

DA-CS-dil_mp32_45

Wiring diagrams

eaton-contactors-dilmp-wiring-diagram.eps

eaton-contactors-contact-dilem-wiring-diagram.eps

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Operating frequency

5000 mechanical Operations/h (AC operated)
5000 mechanical Operations/h (DC operated)

Pollution degree

3

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30
Damp heat, constant, to IEC 60068-2-3

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

8000 V AC

Utilization category

AC-1: Non-inductive or slightly inductive loads, resistance furnaces
AC-3: Normal AC induction motors: starting, switch off during running

Connection

Screw terminals

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

-25 °C

Ambient storage temperature - max

80 °C

Ambient storage temperature - min

-40 °C

Assigned motor power at 115/120 V, 60 Hz, 1-phase

2 HP

Assigned motor power at 200/208 V, 60 Hz, 3-phase

7.5 HP

Assigned motor power at 230/240 V, 60 Hz, 1-phase

5 HP

Assigned motor power at 230/240 V, 60 Hz, 3-phase

10 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

15 HP

Assigned motor power at 575/600 V, 60 Hz, 3-phase

20 HP

Conventional thermal current ith (1-pole, enclosed)

105 A

Conventional thermal current ith (3-pole, enclosed)

36 A

Conventional thermal current ith at 55°C (3-pole, open)

40 A

Conventional thermal current ith of main contacts (1-pole, open)

117 A

Equipment heat dissipation, current-dependent Pvid

13.2 W

Heat dissipation capacity Pdiss

0 W

Heat dissipation per pole, current-dependent Pvid

4.4 W

Application

Contactors for 4 pole electric consumers

Product category

Contactors

Protection

Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)

Electrical connection type of main circuit

Screw connection

Screwdriver size

2, Terminal screw, Pozidriv screwdriver

0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver

Voltage type

AC

Degree of protection

IP00

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

1

Number of contacts (normally closed) as main contact

0

Number of contacts (normally open contacts)

1

Number of main contacts (normally open contact)

4

Rated breaking capacity at 220/230 V

250 A

Rated breaking capacity at 380/400 V

250 A

Rated breaking capacity at 500 V

250 A

Rated breaking capacity at 660/690 V

144 A

Rated control supply voltage (Us) at AC, 50 Hz - max

110 V

Rated control supply voltage (Us) at AC, 50 Hz - min

110 V

Rated control supply voltage (Us) at AC, 60 Hz - max

120 V

Rated control supply voltage (Us) at AC, 60 Hz - min

120 V

Drop-out voltage

AC operated: 0.6 - 0.4 x UC, AC operated

Overvoltage category

III

Duty factor

100 %

Lifespan, mechanical

10,000,000 Operations (DC operated)

10,000,000 Operations (AC operated)

Pick-up voltage

0.85 - 1.1 V AC/DC x Us

0.8 - 1.1 V AC x Uc

Power consumption, pick-up, 50 Hz

50 VA, Dual-frequency coil in a cold state and 1.0 x Us

Safe isolation

440 V AC, Between coil and contacts, According to EN 61140

440 V AC, Between the contacts, According to EN 61140

Power consumption, pick-up, 60 Hz

50 VA, Dual-frequency coil in a cold state and 1.0 x Us

40 W, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz

Residual current

1 mA (with actuation of A1 - A2 by the electronics with "0" signal)

Screw size

M3.5, Terminal screw, Control circuit cables

M5, Terminal screw, Main cables

Power consumption, sealing, 50 Hz

2.1 W, Dual-frequency coil in a cold state and 1.0 x Us

Power consumption, sealing, 60 Hz

2.1 W, Dual-frequency coil in a cold state and 1.0 x Us

8 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz

Terminal capacity (stranded)

1 x 16 mm², Main cables

Switching capacity (auxiliary contacts, general use)

10 A, 600 V AC, (UL/CSA)

1 A, 250 V DC, (UL/CSA)

Switching capacity (auxiliary contacts, pilot duty)

A600, AC operated (UL/CSA)

P300, DC operated (UL/CSA)

Terminal capacity (flexible with ferrule)

1 x (0.75 - 16) mm², Main cables

2 x (0.75 - 10) mm², Main cables

1 x (0.75 - 2.5) mm², Control circuit cables

2 x (0.75 - 2.5) mm², Control circuit cables

Shock resistance

10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

Terminal capacity (solid)

1 x (0.75 - 4) mm², Control circuit cables

2 x (0.75 - 10) mm², Main cables

2 x (0.75 - 2.5) mm², Control circuit cables

1 x (0.75 - 16) mm², Main cables

Terminal capacity (solid/stranded AWG)

18 - 14, Control circuit cables

18 - 6, Main cables

Switching capacity (main contacts, general use)

40 A, Maximum motor rating (UL/CSA)

Tightening torque

1.2 Nm, Screw terminals, Control circuit cables

3 Nm, Screw terminals, Main cables

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Rated insulation voltage (Ui)

690 V

Rated making capacity up to 690 V (cos phi to IEC/EN 60947)

350 A

Rated operational current (Ie) at AC-1, 380 V, 400 V, 415 V

45 A

Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V

25 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

25 A

Rated operational current (Ie) at AC-3, 440 V

25 A

Rated operational current (Ie) at AC-3, 500 V

25 A

Rated operational current (Ie) at AC-3, 660 V, 690 V

15 A

Rated operational current (Ie) at AC-4, 400 V

15 A

Rated operational current (Ie) at DC-1, 110 V

45 A

Rated operational current (Ie) at DC-1, 220 V

45 A

Rated operational current (Ie) at DC-1, 60 V

45 A

Rated operational current for specified heat dissipation (In)

45 A

Rated operational power at AC-1, 220/230 V, 50 Hz

16 kW

Rated operational power at AC-1, 240 V, 50 Hz

18 kW

Rated operational power at AC-1, 380/400 V, 50 Hz

28 kW

Rated operational power at AC-1, 415 V, 50 Hz

31 kW

Rated operational power at AC-1, 440 V, 50 Hz

33 kW

Rated operational power at AC-1, 500 V, 50 Hz

37 kW

Rated operational power at AC-1, 690 V, 50 Hz

49 kW

Rated operational power at AC-3, 240 V, 50 Hz

8.5 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

11 kW

Rated operational power at AC-3, 415 V, 50 Hz

14.5 kW

Rated operational power at AC-4, 380/400 V, 50 Hz

7 kW

Rated operational power (NEMA)

11 kW

Rated operational voltage (Ue) at AC - max

690 V

Resistance per pole

2.7 mΩ

Static heat dissipation, non-current-dependent Pvs

2.1 W

Stripping length (control circuit cable)

10 mm

Stripping length (main cable)

10 mm

Switching time (AC operated, make contacts, closing delay) - max

22 ms

Switching time (AC operated, make contacts, closing delay) - min

16 ms

Switching time (AC operated, make contacts, opening delay) - max

14 ms

Switching time (AC operated, make contacts, opening delay) - min

8 ms

Short-circuit current rating (basic rating)

5 kA, SCCR (UL/CSA)

125 A, max. CB, SCCR (UL/CSA)

125 A, max. Fuse, SCCR (UL/CSA)

Short-circuit current rating (high fault at 480 V)

10/65 kA, CB, SCCR (UL/CSA)

125/70 A, Class J, max. Fuse, SCCR (UL/CSA)

50/32 A, max. CB, SCCR (UL/CSA)

10/100 kA, Fuse, SCCR (UL/CSA)

Short-circuit current rating (high fault at 600 V)

50/32 A, max. CB, SCCR (UL/CSA)

10/100 kA, Fuse, SCCR (UL/CSA)

10/22 kA, CB, SCCR (UL/CSA)

125/100 A, Class J, max. Fuse, SCCR (UL/CSA)

Short-circuit protection rating (type 1 coordination) at 400 V

100 A gG/gL

Short-circuit protection rating (type 1 coordination) at 690 V

50 A gG/gL

Short-circuit protection rating (type 2 coordination) at 400 V

35 A gG/gL

Short-circuit protection rating (type 2 coordination) at 690 V

35 A gG/gL

Special purpose rating of ballast electrical discharge lamps

40 A (600V 60Hz 3phase, 347V 60Hz 1phase)

40 A (480V 60Hz 3phase, 277V 60Hz 1phase)

Special purpose rating of definite purpose rating

150 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)

25 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)

Special purpose rating of elevator control

17 A, 600 V 60 Hz 3-ph, (UL/CSA)

10 HP, 480 V 60 Hz 3-ph, (UL/CSA)

14 A, 480 V 60 Hz 3-ph, (UL/CSA)

15.2 A, 240 V 60 Hz 3-ph, (UL/CSA)

5 HP, 240 V 60 Hz 3-ph, (UL/CSA)

15 HP, 600 V 60 Hz 3-ph, (UL/CSA)

3 HP, 200 V 60 Hz 3-ph, (UL/CSA)

11 A, 200 V 60 Hz 3-ph, (UL/CSA)

Special purpose rating of refrigeration control (CSA only)

40 A, FLA 480 V 60 Hz 3phase; (CSA)

180 A, LRA 600 V 60 Hz 3phase; (CSA)

30 A, FLA 600 V 60 Hz 3phase; (CSA)

240 A, LRA 480 V 60 Hz 3phase; (CSA)

Special purpose rating of resistance air heating

40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)

40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)

Special purpose rating of tungsten incandescent lamps

40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)

40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)

Conventional thermal current ith at 40°C (3-pole, open)

45 A

Conventional thermal current ith at 50°C (3-pole, open)

41 A

Conventional thermal current ith at 60°C (3-pole, open)

39 A

Rated operational power at AC-3, 440 V, 50 Hz

15.5 kW

Rated operational power at AC-3, 500 V, 50 Hz

17.5 kW

Rated operational power at AC-3, 690 V, 50 Hz

14 kW

Actuating voltage

110 V 50 Hz, 120 V 60 Hz

Altitude

Max. 2000 m

Operating voltage at AC, 50 Hz - min

24 V

Operating voltage at AC, 50 Hz - max

690 V

Operating voltage at AC, 60 Hz - min

24 V

Operating voltage at AC, 60 Hz - max

690 V

Powering Business Worldwide

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia