

Product data sheet

Specifications



Repacked Complete joystick controller, Harmony XD2, 30mm, 2 directions, 1 C/O per direction

XD2AC221W



This repacked option saves 1.543 over the standard condition

Main

Range of product	Harmony XD2
Product or component type	Complete joystick controller
Device short name	XD2
Mounting diameter	30 mm
Bezel material	Chromium plated metal

Complementary

Operator position information	All positions
Notch per direction	1
Operator direction information	2 directions
Contacts type and composition	1 C/O for snap action
Short-circuit protection	10 A gG (gl) Neozed cartridge fuse conforming to IEC 60947-5-1
Connections - terminals	Captive screw clamp terminals, 2 x 1.5 mm ² with or without cable end Captive screw clamp terminals, 1 x 2.5 mm ² with or without cable end
Electrical durability	1000000 cycles, AC-15 at 230 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, AC-15 at 127 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, DC-13 at 24 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, DC-13 at 48 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, DC-13 at 120 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 1000000 cycles, AC-15 at 48 V, operating rate <3600 cyc/h, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
Contact code designation	A600-Q600
Overvoltage category	Class I conforming to IEC 61140
Mechanical durability	1000000 cycles
fixing center	60 x 100 mm
Return	to 0 position
Height	111 mm
Depth	68 mm
Product weight	0.22 kg

Environment

Standards	IEC 60947-5-1
-----------	---------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product certifications	CSA
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
IP degree of protection	IP40 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	7.000 cm
Package 1 Length	12.000 cm
Package 1 Weight	243.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

2 kg CO2 eq.

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins