




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **5.21 mm [.205 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	5.21 mm[.205 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	2 – 7 kgf

Dimensions

Product Length	17.5 mm[.688 in]
Compatible Insulation Diameter Range	2.2 – 3.2 mm[.085 – .126 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4150017-2
OCEAN-2.0-APPLICATOR-E-090F140F-REA

TE Part # 170181-4
205 FASTON,REC.,22-18 AWG,BR

TE Part # 42197-2
205 FASTON REC 22-18 AWG TPBR

TE Part # 7-4150017-7
OCEAN_2.0_SPARE_PART_KIT-090F140F

TE Part # 4150017-1
OCEAN-2.0-APPLICATOR-E-090F140F-REM

TE Part # 42239-4
205 FASTON REC 18-14 AWG PHBZ

Also in the Series | FASTON 205

Crimp Terminal Housings(3)

PCB Terminals(10)

Quick Disconnects(35)

Customers Also Bought



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING

TE Part #1827855-1
0.50 SERIES CONNECTER
RECEPTACLE CONTACT

TE Part #5102159-1
A/L UNIV HDR 10P RA

TE Part #2294689-1
0.5/1.0 SEALED PLUG ASSY 51POS

TE Part #796949-6
6 POS TERMI-BLOK PCB MOUNT

TE Part #5104338-1
A/L LOW PRO HDR 10P VERT HT

TE Part #1-6437158-3
FSN-11.5A

TE Part #1761681-6
IDC LOW PRO HDR 16P VERT HT
BLACK

TE Part #2-1437624-4
PKB90B1/4=KNOB PLASTIC W/SKIRT

Documents

Product Drawings
205 FASTON,REC.,22-18 AWG,BR
Japanese

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_170181-2_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_170181-2_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_170181-2_F.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

UL Report

English