



**Part Number :** [2216260121](#)

**Product Description :** Micro-Fit+ OCP M-PIC 12V Receptacle Housing, 24 Circuits (12 Power, 12 Signal), Black

**Series Number :** 221626

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[2216260121\\_sd.pdf](#)

[2216260001-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[2217510001-AS-000.pdf](#)


[2217510001-PS-000.pdf](#)

[2217510001-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	221626
Description	Micro-Fit+ OCP M-PIC 12V Receptacle Housing, 24 Circuits (12 Power, 12 Signal), Black
Application	Power, Signal, Wire-to-Board
Product Name	Micro-Fit+ OCP M-PIC
UPC	198282687719

### Physical

Circuits (maximum)	24
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.230/g
Number of Rows	3
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	3.00mm, 1.50mm
Pitch - Termination Interface	3.00mm, 1.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Fit+ OCP M-PIC Vertical Three Row Through Hole Headers	<a href="#"><u>221591</u></a>
Micro-Fit+ OCP M-PIC Right-Angle Three Row Through Hole Headers	<a href="#"><u>221751</u></a>

### Use with Part(s)

Description	Part Number
Micro-Fit+ OCP M-PIC Power Crimp Female Terminals	<a href="#"><u>224179</u></a>
Micro-Fit+ PCIe CEM5 Female Signal Crimp Terminals	<a href="#"><u>219197</u></a>