




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 10

Primary Product Color: Natural

Protection & Strain Relief Accessory Type: Cover

Primary Product Material: PBT GF15

Strain Relief: Without

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
---	-------

Configuration Features

Compatible With Connector Code	B
Number of Positions	10

Body Features

Primary Product Color	Natural
Primary Product Material	PBT GF15

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Method	Bulk
------------------	------



Packaging Quantity

2000

Other

Serviceable	No
-------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #2372884-2
3POS,FASTIN-ON 2.8,REC HSG,
GLASS ACT



TE Part #1-968562-2
10POS MQS REC



TE Part #1217281-2
FF 110 REC 24-20AWG TPBR



TE Part #1379662-2
12W PLUG HSG ASSY GRAY



TE Part #2208339-3
10POS,NANOMQS,REC HSG,COD C



TE Part #2319297-1
025RF 19P PLUG ASSY NAT



TE Part #CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING

Documents

Product Drawings
COVER,10 POS. MQS,NA
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2-2177198-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2-2177198-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2-2177198-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English