

## Features

- Extra Heavy Duty
- Industrial castor
- Rotation Swivel
- Fixing Plate
- Polyurethane
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

## RS PRO Castor Wheels

RS Stock No.: 0149298



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description









Wheel coated with polyurethane AVOLAN 91 Shore A. Black mechanical cast iron centre. Hub on shielded ball bearings. Assembled with central spacer. In pressed and welded steel, high thickness, turning on thrust and tapered roller bearings.

## General Specifications

Rotation	Swivel
Weight Class	Extra Heavy Duty
Load Capacity (Kg)	650
Load Capacity / 4pcs (Kg)	2600
Tyre Material	Polyurethane
Hub Material	Cast Iron
Bracket Material	Pressed Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

## Operation Environment Specifications

Operating Temperature (Celsius)	-20° to 80°
---------------------------------	-------------

							
150x50	135x110	105x80	13	50	205	650	820

## Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	150
Wheel / Tread Width (mm)	50
Overall Height (mm)	205
Number of Fixing Holes	4
Fixing Hole Size (mm)	13
Hub Bearing Type	Ball Bearing
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	91
Levelling Extent (mm)	
Offset (mm)	50
Castor Weight (Kg)	5.120

## Fixing Centres Specifications

Fixing Centres (mm)	105x80
Fixing Centres Length (mm)	105
Fixing Centres Width (mm)	80

## Fixing Plate Specifications

Fixing Plate Dimensions (mm)	135x110
Fixing Plate Length (mm)	135
Fixing Plate Width (mm)	110