



Pushing Performance
Since 1945

MPP ix Type A - RJ45 IP20 Cat6A PUR 2,5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 344 7804 025
Specification	MPP ix Type A - RJ45 IP20 Cat6A PUR 2,5m
HARTING eCatalogue	https://harting.com/33483447804025

Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING Mini PushPull
	HARTING ix Industrial® Type A
	Overmoulded IDC termination
Connector 2	HARTING DualBoot RJ45 Piercing termination
Type of cable	Copper cable (round)

Version

Cable length	2.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC insulation displacement termination Piercing termination

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
------------------------------	--



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C
Cable diameter	6.7 mm ± 0.3 mm

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow

Specifications and approvals

Specifications	UN/ECE-R 118
	IEC 60332-1-2 Flame retardancy
	UL 1581, Sec. 1090 (H) Flame retardancy
	EN 60811-404 Oil resistance
	UL style 21815
	IEC 60754-2 Halogen freeness
	EN 50618 UV resistant

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140796775
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600