



Connectors > Modular Jacks & Plugs > RJ14 Connectors



Port Configuration: **Single Port**

Port Matrix Configuration: **1 x 1**

Connector Profile: **Standard**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Cable-to-Board
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack

Configuration Features

Number of Positions	6
Port Configuration	Single Port
Port Matrix Configuration	1 x 1
Connector Contact Density	Standard
PCB Mount Orientation	Vertical
Number of Loaded Positions	4

Body Features

Connector Profile	Standard
Modular Jack Latch Orientation	Standard - Latch Down



Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to PCB	Surface Mount
Termination Post & Tail Length	2.5 mm[.1 in]

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.02 mm[.04 in]
Mating Entry Location	Top
Housing Color	Black
Housing Material	PA 9T GF

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	12.7 mm[.5 in]

Usage Conditions

Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

Performance Category	Cat 3
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Reel, Tape Mounted on Reel
Packaging Quantity	300



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought




TE Part #292161-9
CT P/HDR ASSY V 9P W/KINK NAT




TE Part #5520257-2
MJ,TE,4P,PNL STOPS



TE Part #215307-8
2X8P HV100 REC CON. TE, 7.0MM



TE Part #CAT-3983178-PHBXVD
CT 2mm Post Header Asmbly: Box V DIP



TE Part #063209-E
SMCQ 26 M AB VV 3-03 CLHD * H007 137 E00



TE Part #2334884-1
UMCC Micro-Coax receptacle, Gen 4



TE Part #5747847-4
37 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #2-1825910-2
FSM12JH=6MM TACT SWITCH, HIGH TEMP



TE Part #5520259-4
MJ,TE,8P,TRAYS

Documents

Product Drawings
6/4 INV.MOD JACK

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-338086-4_Z.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1-338086-4_Z.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-338086-4_Z.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



1-1773464-9_MODULAR_JACKS_SINGLE_PORT_PCB_MOUNT

English

Product Specifications

AMP surface mount modular jack

English

Application Specification

English

Agency Approvals

UL Report

English