

#### **FEATURES**

- Maximum operating temperature of 70°C
- A voltage rating of 600V
- 25m length
- Single core cable design

# RS PRO Blue Single Core x 10.0sqmm (Class 5 PCW), PVC Insulated, 600/1000V, Type BK, 25m

RS Stock No.: 516-7978



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

From RS PRO, comes a range of high quality and great value Tri-rated cables. Manufactured with a premium annealed copper conductor and insulated with PVC (Polyvinyl Chloride), these Tri-rated cables are a fantastic solution for use in control panels and other types of electrical equipment

### **General Specifications**

Туре	BK	
Tri-rated	Yes	
Sheath Colour	Blue	
Fire Behaviour	Flame Retardant	
Application	Electrical cabinets, Industrial electrical installations, Small electronic devices, Relay and instrumentation panels, Control metering, Motor starters	

#### **Electrical Specifications**

Voltage Rating	600/1000V
Current Rating	68A
Conductor Material	72/0.40mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation Material	PVC (Type TI1 to BS EN 50363)
Conductor Resistance	1.91 Ω/km @ 20°C (Maximum)



## **Mechanical Specifications**

Length	25m	
Cross Sectional Area	10mm <sup>2</sup>	
Outer Diameter	7.2mm	
American Wire Gauge	7	
Core Strands	80/0.4mm	
Size of Strands	0.4mm	
Insulation Wall Thickness	1.00mm (Nominal)	
Weight	112.90kg/km	
Diameter Over Insulation	Lower Limit: 5.70mm;Upper Limit: 7.20mm	

## **Operation Environment Specifications**

Temperature Range	-15 to +70°C	
-------------------	--------------	--

## Approvals

Standards Met	BS 6231:2006

