

# Product data sheet

## 6110-1 CT

EAN-No. 4000896025022



Length: 335 mm · Torque range min-max: 5 – 60 Nm · Accuracy: 2 % ·  $\pm 10$  %



- **Accuracy  $\pm 2$  % of the scale value** (in direction of actuation for right-hand tightening)  
For left-hand tightening, use our torque wrenches with insert tool
- **HiPer fine-tooth reversible ratchet** in 6121-1CT · 6122-1CT · 6123-1CT (90 teeth · 4° operating angle)
- High-precision premium torque tools – for the highest demands
- **Hard chrome-plated** steel tube construction – slim, but very sturdy and wear-resistant
- Secure storage in safe box with inspection window
- Safe:
  - Haptic (close-gap release)
  - Audible ("click" sound)
- User-friendly reversible ratchet  
**Service-friendly** (do-it-yourself repair sets for ratchets available)
- Integrated shift lever
- Safe and fast adjustment of the desired torque value by turning the handle
- Knob for additionally locking the set value
- Ergonomically shaped handle with collar **reduces the risk of slipping-off and injury**
- Accuracy – fine scale graduation
- With calibration certificate and serial number
- Surface: hard chrome plated
- DIN EN ISO 6789-2:2017, DIN 3120, ISO 1174-1
- Made in Germany
- Output:  $\pm 10$  %
- Dimensions: 335 mm
- Net weight: 0.56 kg
- For manual operation
- Torque range min-max: 5 – 60 Nm
- Accuracy: 2 %
- Scale Graduation (Nm): 0.5 Nm
- Actuating force min.-max. kg: 1.9 – 24.7 kg
- Number of teeth: 90 (Opening angle 4°)
- Head Thickness a: 14.5 mm
- Head Width b: 32 mm
- **No more turning back:** Continuous long-term tests on the 5000 series and 6000 series of HAZET torque wrenches have demonstrated that turning them back to the smallest scale value is not required

SYSTEM 6000-1 CT industrial torque wrench · 1 – 2000 Nm · with reversible ratchet · accuracy  $\pm 2 / 4$  %