

Product Information



2845QMP125P30-13

EAN 4031582348552

Walkway castor with integrated brake shoe for moving walkways, threadguards with integrated brake shoe, housing made of pressed steel, bright zinc plated, blue passivated, precision ball bearing in swivel head, wheel axle with nut, Wheel centre made of Polyurethane, Tread: Polyurethane, 4 tracks, selfcleaning between tracks, with threadguards, precision ball bearing, distances between tracks: approx. 4,5 mm, track width: approx. 4,0 mm.

Hint:

Load capacity 80 kg per castor on level and securely attached floors, 40 kg per castor on walkways.

Please note that according to EN1929 only castors with a minimum wheel diameter of 120 mm can be used on walkways.



Technical Data

Wheel diameter	125 mm
Width of Tread	32 mm
Centre hole	13 mm
Offset	38 mm
Swivel Interference	100 mm
Overall height	155 mm
Temperature	- 40 / + 60 °C
Standard	EN 12530
Weight	0.671 kg
Hardness of tread	D 59 Shore
Load capacity	80 kg
Load capacity (static)	160 kg

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

2845QMP125P30-13

EAN 4031582348552

