

Specifications

Eaton 40ET

Eaton Bussmann series high speed British standard fuse, high speed, 40 A, AC 690 V, DC 500 V, BS88, 19 x 77 mm, aR, BS

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	40ET
EAN	5027590480093
UPC	051712831062
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	39.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide

Electrical data

AMPERAGE RATING	40 A
VOLTAGE RATING	690 V
INTERRUPT RATING	200 kAIC
PRE ARC (I2T)	103
CLEARING (I2T)	600
WATT LOSSES	9 W

Product specifications

APPLICATION	protection of DC common bus, DC drives, power converters/rectifiers and reduced voltage starters
FUSE INDICATOR	None

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250044en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-8-80a-et.stp
TECHNICAL DATA SHEETS	720024 CT, ET, FE, EET, FEE, FM, FMM, MT, MMT fuses

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

