


Product description	<b>M8 Female cable connector, Contacts: 3, unshielded, moulded on the cable, IP67/IP69K, UL 2238, PUR, black, 3 x 0.34 mm<sup>2</sup>, 2 m</b>
Area	<b>M8</b>
Coding	<b>A-coded</b>
Series	<b>718</b>
Part no.	<b>77 3406 0000 50003-0200</b>


### Illustration



### Scale drawing



### Contact arrangement (Plug-in side)



### Cable length tolerance

<i>cable length</i>	<i>tolerance</i>
≥ 0,10 m	+ 0,03 m
≥ 0,20 m	+ 0,04 m
≥ 0,50 m	+ 0,07 m
≥ 1,00 m	+ 0,10 m
≥ 2,00 m	+ 0,15 m
≥ 5,00 m	+ 0,20 m
≥ 10,0 m	+ 0,25 m
≥ 20,0 m	+ 0,35 m

### Technical data

#### General features

Part no.	<b>77 3406 0000 50003-0200</b>
Notice	Alternative part no.: 79 3406 52 03 Please note that, due to the change from the old to the new order number, there may be deviations in the technical specifications. For questions about product details, please use the 'Contact Customer Service' form on the right.
Connector design	Female cable connector
Type standard	DIN EN 61076-2-104
Coding	A-coded
Cable length	2 m (Standard 2 m and 5 m. Other lengths are available on request.)
Version	Connector socket straight
Connector locking system	screw
Termination	moulded on the cable
Degree of protection	IP67/IP69K
Connection cross-section	0.34 mm <sup>2</sup> / AWG 22
Temperature range from/to	-25 °C / 85 °C

Product description	<b>M8 Female cable connector, Contacts: 3, unshielded, moulded on the cable, IP67/IP69K, UL 2238, PUR, black, 3 x 0.34 mm<sup>2</sup>, 2 m</b>
Area	<b>M8</b>
Coding	<b>A-coded</b>
Series	<b>718</b>
Part no.	<b>77 3406 0000 50003-0200</b>

Mechanical operation	> 100 Mating cycles
Weight (g)	175.22
Customs tariff number	85444290
Country of Origin	DE

### Electrical parameters

Rated voltage	50 V (AC) / 60 V (DC)
Rated impulse voltage	1500 V
Rated current	4.0 A
Pollution degree	3
Overvoltage category	II
Insulating material group	II
EMC compliance	unshielded

### Material

Housing material	PUR
Contact body material	PUR
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	Zinc die-cast nickel-plated
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	9686478e-f903-453c-9dfa-644071f991f2

### Cable data - Structure of the cable

Cable diameter	4.3 mm
Cross section	3 x 0.34 mm <sup>2</sup>
Sheath material	PUR
Single-lead insulation	PP9Y halogen-free
Single-lead structure	43 x 0.10 mm
Cable color	black

### Cable data - Electrical properties

Conductor resistance	60 Ω/Km (20°C)
----------------------	----------------

### Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	> 5 million
Permitted acceleration	≥ 5 m/s <sup>2</sup>
Travel distance, horizontal	≥ 5 m
Travel distance, vertical	≥ 5 m
Travel speed	≤ 200 m/min

Product description	<b>M8 Female cable connector, Contacts: 3, unshielded, moulded on the cable, IP67/IP69K, UL 2238, PUR, black, 3 x 0.34 mm<sup>2</sup>, 2 m</b>
Area	<b>M8</b>
Coding	<b>A-coded</b>
Series	<b>718</b>
Part no.	<b>77 3406 0000 50003-0200</b>

### Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 80 °C
Temperature range cable fixed from/to	-50 °C / 80 °C

### Cable data - Other features

Halogen free	yes
--------------	-----

### Authorization/approvals

Approvals	UL 2238
-----------	---------

### Classifications

eCl@ss 11.1	27-06-03-11
ETIM 9.0	EC002638

### Declarations of conformity

Low Voltage Directive	2014/35/EU (EN 60529:1991;EN 60204-1:2018)
RoHS Directive	2011/65/EU (EN 50581:2012)

Product description	<b>M8 Female cable connector, Contacts: 3, unshielded, moulded on the cable, IP67/IP69K, UL 2238, PUR, black, 3 x 0.34 mm<sup>2</sup>, 2 m</b>
Area	<b>M8</b>
Coding	<b>A-coded</b>
Series	<b>718</b>
Part no.	<b>77 3406 0000 50003-0200</b>

## General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 40 cNm).