

1110 WMW-2

Tool trolley WorkMo B2

Code	ETIM
2954435	EC000181
EAN	UNSPSC
4010886947272	24-11-24-01
Country of origin	eCl@ss
Germany	21-07-11-00
Customs tariff number	
94039910	



Article description

- Modular tool trolley
- Consisting of: No. 1110 WM 24, 1110 WM 221, 1110 WMR 23 and 1110 WMHP 2
- Mobile as a complete unit or each module individually portable
- Ideal for transportation from the workshop to changing workplaces
- 6 drawers with full extension suitable for GEDORE 1500 ES/1500 CT modules
- For 2x 1/3 modules or 1x 2/3 module
- One compartment with locking device for GEDORE L-BOXX® 136 No. 1100 L (not included)
- Light and sturdy aluminum-plastic mix
- Mobile with roller skids with 4 swivel castors, 2 of them with total brake
- Wooden worktop for assembly work
- Compatible with Sortimo® interior vehicle fittings and load safety
- Crash tested
- Dimensions: H 1140 x B 580 x T 550 mm
- Weight advantage (up to 50 % lighter than comparable solutions!)

Article information

Contents [Qty of pieces]	1	Number of lengthwise dividers	optionally available
Net weight [kg]	42,6 kg	Number of drawers	6
Total length [mm]	580 mm	Thickness (e.g. workplate)	20 mm
Total width [mm]	550 mm	Worktop dimensions	572 x 426 x 41 mm
Total height [mm]	1.140 mm	Swivel castor diameter with brakes (2x)	100
Material	Aluminium-Kunststoffmix	Single pull-out stop	no
Dimension (L x W x H)	1.140 mm x 550 mm x	Number of wheels	4
Load capacity kg	150 kg	Working height	1.140
Number of crosswise dividers	optionally available		