



JKL PART NUMBER	LENGTH A +/- 2mm	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms) @ 0°C	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) AVERAGE
BF350-20B	50mm	RGB HIGH OUTPUT WHITE 5400° KELVIN (REF.) x = .340 y = .360	425	170	5 ± 1	28000 ± 2800	40,000
BF375-20B	75mm		515	205	5 ± 1	28000 ± 2800	40,000
BF386-20B	86mm		540	215	5 ± 1	28000 ± 2800	40,000
BF3100-20B	100mm		640	255	5 ± 1	28000 ± 2800	40,000
BF3115-20B	115mm		725	290	5 ± 1	28000 ± 2800	40,000
BF3130-20B	130mm		775	310	5 ± 1	28000 ± 2800	40,000
BF3160-20B	160mm		900	360	5 ± 1	28000 ± 2800	40,000
BF3180-20B	180mm		950	380	5 ± 1	28000 ± 2800	40,000
BF3216-20B	216mm		1125	450	5 ± 1	28000 ± 2800	40,000
BF3240-20B	240mm		1240	495	5 ± 1	28000 ± 2800	40,000
BF3250-20B	250mm		1300	520	5 ± 1	28000 ± 2800	40,000
BF3275-20B	275mm		1475	590	5 ± 1	28000 ± 2800	40,000
BF3300-20B	300mm		1625	650	5 ± 1	28000 ± 2800	40,000
BF3360-20B	360mm		1850	740	5 ± 1	28000 ± 2800	40,000
BF3380-20B	380mm		1975	790	5 ± 1	28000 ± 2800	40,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

G ELECTRICAL MODIFICATIONS		8/5/04	 THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	 JKL COMPONENTS CORPORATION					
F	ADD PART NUMBER BF3115-20B	12/19/02			TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP					
E	ADD PART NUMBER BF3180-20B & BF3380-20B	11/30/01	DRAWN BY	APP'VD BY	DATE	SIZE	FSCM NO.	DRAWING NO.		
D	ADD PART NUMBER BF3240-20B	4/26/01	L. WENGSTROM	J.K.	8/5/04	A	55335	BF 3-20B		
C	ADD PART NUMBER BF3130-20B	9/11/00	- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
B	ADD PART NUMBER BF375-20B	4/21/00	MANUAL REVISIONS NOT PERMITTED			NONE	2/21/00	8/5/04	G	1 OF 1
A	LENGTH ±5 TO ±2	2/25/00								
	RELEASED - CANCEL BF-3mm DIA DRAWING	2/21/00								
REV. NO.	DESCRIPTION/ECO NUMBER	APP'VD DATE								