

DH 24PB3 **Rotary Hammer (SDS-PLUS)**

- New and powerful design and class-top drilling speed
thanks to the efficient transmission of the hammering energy
- 800W Hitachi powerful motor
- Long service life and high durability thanks to Internal pressure adjustment mechanism
- Idle hammering prevention mechanism
- Equipped with a sealed type ball bearing for improved resistance to grease leakage
- One-push tool retainer eliminates the need for sliding the grip to mount the bit
- Non-slip double-layer molded handle and gear cover
- Compact body: Entire length 351mm(13-13/16")
- Push-button type forward-reverse changeover switch
- Slip-clutch mechanism
- Auto-stop carbon brush
- 2-mode action: Hammer drilling and drilling only



Specifications:

Capacity	Concrete	3.4 - 24mm (1/8" - 15/16")
	Steel	13mm (1/2")
	Wood	32mm (1-1/4")
Power Input	800W	(120V : 7.0A)
No-Load Speed	Forward: 0 to 1,050 /min.	Reverse: 0 to 550 /min.
Full-load impact rate	0 to 4,600 /min.	
Overall Length	351mm (13-13/16")	
Weight	2.3 kg (5.1 lbs.)	
Standard Accessories	1 Plastic case 1 Side handle 1 Depth gauge	

Note: Manufacturer reserves the right to change specifications of parts and accessories without notice. Standard accessories of parts may vary from country to country.